

ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



Overview

100 years estimated archive life for all data files*

The ODS-D280F Optical Disc Archive fibre channel drive unit works with the ODS-L30M/L30E/L100E PetaSite scalable library. The drive is part of the Optical Disc family of data storage products designed to provide an extended life cycle for storing and archiving all forms of audio-visual assets and data files for the very long term.

* Referring to the ISO/IEC16963 method, this is the estimated average archival life of an archival bare disc calculated by internal acceleration testing.

Deep archive for very long-term archiving requirements

Fully backward-read compatible, the Sony Optical Disc Archive drive technology is designed to provide read capability for all generations of optical disc cartridge media, giving you access to your content for 50+ years, whilst eliminating the need for a forced media migration due to media and drive obsolescence.

Reliable and robust large-capacity media

The drive unit handles a single optical disc cartridge that offers an alternative to LTO or traditional forms of data tape for the longer-term archiving of valuable assets. With a low total cost of ownership, the Sony optical disc cartridge offers very fast random access to all content and files. The innovative drive design provides for a 'dual channel' capability and, being file format independent, it can store your assets in a data file format. Sony optical disc cartridges are available in 300 GB, 600 GB, 1.2 TB, 1.5 TB and 3.3TB* capacity sizes, in re-writable and write-once formats.

* 3.3TB ODC-3300R (Generation 2) cartridge is write-once. The 3.3TB cartridge is only readable/writable by the ODS-D280U and the ODS-D280F drives. The ODS-D55U, the ODS-D77U and the ODS-D77F drives cannot handle the 3.3TB cartridge.

Ideal for deep archive and near-online archive

The Sony Optical Disc Archive system is ideal for deep archive for very long term archiving, such as broadcaster archives where data tape does not provide the assurance or meet the need for write-once, very long-term archive requirements. It provides second copy archive at a remote site and is ideal for business continuity/disaster recovery, post house and production back-up and for video, film and stock footage archives or national archives. The system can also be used for news and sports clips that need to be near-online and as an on-line browse and proxy clip store.

A world of solutions

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy,

reliable access to your precious data is crucial – along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

Features

Very fast transfer speeds for ODS-L30M/L60E/L100E PetaSite scalable library

The ODS-D280F has very high transfer speeds. Reading is maximum 2Gbps*. Writing is maximum 1Gbps (with verify on)*. Performance is varied based on type of cartridges.

* When using 3.3TB ODC-3300R Generation 2 write-once cartridge.

Optical disc cartridges mounted as a single large volume making file access very simple

The Sony optical disc cartridge system is designed and manufactured to extremely high specifications, offering a reliable, robust and portable media system for the very long term. Optical disc cartridges are available in 300 GB, 600 GB, 1.2 TB, 1.5 TB and 3.3TB* capacity sizes, in re-writable and write-once formats.

* 3.3TB ODC-3300R (Generation 2) cartridge is write-once. The 3.3TB cartridge is only readable/writable by the ODS-D280U and the ODS-D280F drives. The ODS-D55U, the ODS-D77U and the ODS-D77F drives cannot

handle the 3.3TB cartridge.

Related products



ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



File Server mode License for FM2

File Server mode License of FM2(FSL) is an option license for File Manager2.
 The license enables standard file IO interface of File Manager2, and it can be usable by local or network applications (SMB).



Optical Disc Archive Cartridge Generation 2

ODC-3300R 3.3TB write-once cartridge



ODS-L60E

PetaSite Optical Disc Archive library expansion unit (drive and cartridge)



ODS-D380U

The latest Optical Disc Archive stand-alone drive with very high transfer speeds of 1.5 Gbps write (verify on) and 3 Gbps read using ODC-5500R Generation3 cartridge.



ODS-L100E

PetaSite Optical Disc Archive library expansion unit (cartridge only)




ODS-D280U

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.



Virtual Tape mode License for FM2

Virtual Tape mode License for FM2, (VTL), is a option license of File Manager2. The license enables tape protocol interface of File Manager2.



ODS-L30M

PetaSite Optical Disc Archive 30-slot master library unit




Optical Disc Archive Software (Driver)

PC read/write file utility for ODS-D77U/D77F and ODS-D55U Optical Disc Archive systems



ODBK-203

Base unit for Optical Disc Archive ODS-L30M PetaSite scalable library



File Manager2

File Manager2 (FM2) is a successor software to the existing File Manager software. FM2 allows the ability to archive / retrieve your contents to / from Optical Disc Archive Drive and Petasite Library from a PC.



ODBK-201

Power supply unit for Optical Disc Archive ODS-L30M/L60E PetaSite scalable library



ODBK-103

Extension Kit for Optical Disc Archive ODS-L30M PetaSite scalable library



ODBK-202

Base unit for Optical Disc Archive ODS-L30M PetaSite scalable library

Gallery

