

PSS-650

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range

Up/down position	300~375mm / 11 13/16~14 3/4 inches 475~625 mm / 18 11/16~24 19/32 inches (with Supplied extension pole) (25mm pitch adjustment)
Horizontal angle of rotation	± 10 deg
Left/right tilt angle	± 5 deg (Fine adjustment function with adjustment knob)
Up/down tilt angle	± 5 deg (Fine adjustment function with adjustment knob)
Front/back position	± 50 mm / ± 1 31/32 inches (Fine adjustment function with

adjustment knob)

Left/right position

± 25 mm / $\pm 31/32$ inch (Fine adjustment function with adjustment knob)

Dimensions (W x H x D)

Dimensions (W x H x D)

299 x Height* x 453.5 mm / 11 25/32 x H x 17 27/32 inches

*Height: 300~375mm / 11 13/16~

14 3/4 inches

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

Dimensions (W x H x D) *without protrusions (Adjustment knob)

Dimensions (W x H x D)

*without protrusions

(Adjustment knob)

246 x Height* x 322 mm / 9 11/16 x H x 12 11/16 inches

*Height : 300~375mm / 11 13/16 ~14 3/4 inches

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

Mass

Mass	Approx. 8.6 kg / 19 lb
------	------------------------

Maximum load

Maximum load	30 kg / 66 lb
--------------	---------------

Optional accessories

Optional accessories	PSS-650P
----------------------	----------

Color

Color	Black
-------	-------

Gallery

