

## SRG-A40

PTZ Auto Framing Camera with AI Analytics, 30x (w/ CIZ) zoom, and NDI® | HX capability



### Overview

#### **A Camera that Automatically and Naturally Shoots Video for you**

With the advanced PTZ Auto Framing feature, the camera automatically track the target in a comfortable viewing with smooth pan, tilt, zoom movement regardless of posture, movement and what they are wearing. Since there is no need for dedicated operator, there is system cost advantage.

The SRG-A40 harnesses powerful AI-powered video analytics that can automatically detect and track the position of a presenter within the camera frame. As the presenter moves, the camera's pan/tilt/zoom mechanism ensures that the presenter is always framed accurately and naturally, without the need for a human camera operator to manually follow their movements.

### Features

#### **Automatic and reliable**

With Sony's newly developed AI Analytics unit, it detects the subject's skeleton and tracks the subject, even when there are several people in the frame.

#### **Choice from three shooting modes**

The SRG-A40 has a choice of three shooting modes; Full body, Waist, and Close up. In each mode, you can select the center, left, or right angle of view, and the SRG-A40 can automatically track

the subject in the selected optimal position.

### **Integrated tally lamp**

The SRG-A40 features a built-in tally lamp, just like you'd find on professional studio cameras. The lamp illuminates to give presenters visual confirmation of shooting status, or to show that PTZ Auto Framing mode is active. The lamp colour will change from Red (standby) to Green (PTZ Auto Framing ON).

### **High speed pan/tilt**

Speedy, precise pan/tilt operation ensures that the camera can accurately keep track of the presenter's movements.

### **Wide angle zoom lens**

As well as powerful close-ups, the SRG-A40 can capture broad shots of the presenter or audience with a wide field of view.

### **Clear Zoom**

Digital plus optical zoom increase maximum magnification to a huge 40x for frame-filling close-ups without reducing resolution.

### **4K Exmor R sensor**

The highly sensitive 1/2.5-type image sensor captures crisply-detailed 4K video with extremely low picture noise, even when shooting in low light.

### **IP streaming**

Stream 4K 30p video from the camera with support for popular IP protocols – ideal for live events and webcasts.

### **PoE++ support**

Support for next-generation Power over Ethernet simplifies installation, with camera power, control and IP video all carried by a single LAN cable.

### **HDMI/SDI outputs**

As well as live streaming over IP, the camera can simultaneously

output video via HDMI and SDI for conventional production.

### **Picture Setting File**

Easily copy picture settings across multiple cameras for quick, convenient set-up in multi-camera shooting environments.

### **Remote control of PTZ operation**

Pan/Tilt/Zoom camera movements and other functions can all be precisely controlled using the supplied IR remote commander, for convenient wireless control of PTZ functions without needing additional equipment. It can also be controlled using the optional additional IP500 remote controller, just like professional broadcast cameras.

### **Convenient control from PC or tablet**

Camera functions can also be controlled remotely from a networked PC or tablet\* using our intuitive app.

\*Windows only

### **Easy ceiling mounting**

The camera comes supplied with a mounting plate for convenient ceiling installation if required.

### **Light, compact design**

The camera's stylish, compact body fits unobtrusively into any environment.

### **Choice of colour finishes**

The SRG-A40 is available in a choice of black or white colour finishes, to suit the needs of any application.

## Specifications

### Camera

Image Sensor

1/2.5 type ExmorR CMOS

---

Image Sensor (Number of Effective Pixels)	Approx. 8.5M pixels
Signal System	2160/29.97p, 25p, 23.98p 1080/59.94p, 50p, 29.97p, 25p, 23.98p 1080/59.94i, 50i 720/59.94p, 50p
4K Capability	Yes
Minimum Illumination (50IRE)	1.6 lux (1/30s 50IRE F2 high- sensitivity OFF)
Horizontal Resolution	1700 TV lines (Center) (4K) 1000 TV lines or higher (Center) (FHD)
Gain	Auto/Manual (0 to +48 dB) High Sensitivity On
Shutter Speed	1/1 to 1/10000 sec (59.94 Hz system) 1/1 to 1/10000 sec (23.98 Hz system) 1/1 to 1/10000 sec (50Hz system)
Exposure Control	Auto/Manual/Priority AE (Shutter, Iris)

White Balance	Auto1/Auto2/One Push WB/Indoor/Outdoor/Manual
Zoom Capability	30x (4K with CIZ*1), 40x (HD with CIZ), Max. 80x (HD with CIZ and Tele Convert Mode)
Focusing System	Auto/Manual
Horizontal Viewing Angle	Approx. 70.0 degree (Wide)
Focal Length	f=4.4mm (Wide) to 88.0mm (Tele)
F-number	F2.0 to F3.8
Minimum Object Distance	80 mm (Wide)~ 800 mm (Tele)
Pan/Tilt Angle	Pan: $\pm 170^\circ$ Tilt: $+90^\circ/-20^\circ$
Pan/Tilt Speed (Max.)	Pan: 300 degrees/sec Tilt: 126 degrees/sec
Pan/Tilt Speed	Pan: $1.1^\circ$ to $101^\circ/s$ Tilt: $1.1^\circ$ to $91^\circ/s$
Pan/Tilt Speed (Slow)	Pan: $0.5^\circ$ to $60^\circ/s$ Tilt: $0.5^\circ$ to $60^\circ/s$
Pan/Tilt Slow Mode	Yes

Pan/Tilt Operation Noise	NC30 or less *2
--------------------------	-----------------

Preset Position	256 (CGI) 100 (VISCA)
-----------------	--------------------------

Picture Freeze Preset	Yes
-----------------------	-----

PTZ Motion Sync	Yes
-----------------	-----

## Network

IP Video Resolution	3840x2160, 1920x1080, 1280x720, 640x360
---------------------	--

Compression Format	H.264: High/Main/Baseline Profile H.265: Main Profile
--------------------	--

Maximum Frame Rate	H.264: 60fps H.265: 60fps
--------------------	------------------------------

Bitrate Compression Mode	CBR/VBR (selectable)
--------------------------	----------------------

Range of Bitrate Setting	512 kbps~50 Mbps
--------------------------	------------------

Multi Streaming Capability	3
----------------------------	---

Maximum Number of Clients	5
---------------------------	---

Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, HTTP, HTTPS, DHCP, DNS, RTP/RTCP, RTSP, VISCA over IP, SRT
-----------	---

NDI HX Capability	Yes Option (need to attach a license)
-------------------	--

## Camera Features

Auto ICR (Auto mode of IR Cut filter Removal)	Yes
---	-----

Day/Night	Yes
-----------	-----

Visibility Enhancer	Yes
---------------------	-----

Image Stabilizer	Yes
------------------	-----

Image Flip	Yes
------------	-----

Picture Setting File	Yes
----------------------	-----

Flicker Cancel	On/Off
----------------	--------

Hide OSD Menu	On/Off
---------------	--------

Standby Mode	Yes
--------------	-----

Remote Standby	Yes
----------------	-----

PTZ Auto Framing	Yes
------------------	-----

---

## Web UI

Version Up

Yes

---

Languages

Japanese, English, French,  
Spanish, German, Italian, Chinese,  
Traditional Chinese, Korean,  
Portuguese, Russian, Polish, Hindi,  
Turkish

---

OS and Browser

Windows 11 64-bit w/ Chrome,  
Windows 10 64-bit w/ Chrome,  
Windows 11 64-bit w/ Edge,  
Windows 10 64-bit w/ Edge,  
macOS 11 w/ Chrome,  
macOS 12 w/ Chrome,  
macOS 13 w/ Chrome\*3

---

## Audio

Channel

2ch

---

Audio Codec

AAC LC 128kbps/ST (IP)  
AAC LC 256kbps/ST (IP)

---

Setting Option

Auto level control: On/Off,  
Equalizer: Off/Low cut/Voice  
enhancement,  
Input selection: Microphone/Line,



Mic volume: -10~+10 (21 steps),  
Audio codec

---

Embedded Audio in Baseband Video	Yes (3G-SDI, HDMI)
----------------------------------	--------------------

---

Embedded Audio in IP Streaming	Yes
--------------------------------	-----

---

## Interface

---

4K Video Output	HDMI x1, IP (streaming) x1
-----------------	-------------------------------

---

HD Video Output	3G-SDI x1, HDMI x1, IP (streaming) x1
-----------------	---

---

SD Video Output	IP (streaming) x1
-----------------	-------------------

---

Remote Video Format Switching	Yes
-------------------------------	-----

---

HDMI Color Space	YCbCr, 4:2:2 8bit RGB, 4:4:4 8bit
------------------	--------------------------------------

---

Camera Control Interface	VISCA RS-422 RJ45 (In/Out) VISCA over IP RJ45
--------------------------	--

---

IR Remote Control	Yes
-------------------	-----

---

Microphone Input	Stereo Mini-phone (φ3.5mm) x1,
------------------	--------------------------------

---

(Mic/Line Selectable)

Sync. System	INT
Tally	Front x 1 Red/Green (for PTZ Auto Framing)
Power Connector Type	IEC60130-10 (JEITA standard RC-5320A) Type5

## General

Power Requirements	DC 19.5V PoE++ (IEEE802.3bt type4 class8)
Power Consumption	DC19.5V: 80W PoE++: 71.3W
Operating Temperature	0 °C to 40 °C 32 °F to 104 °F
Storage Temperature	-20 °C to +60 °C -4 °F to +140 °F
Dimensions (W x H x D)*4	156.7 x 184.0 x 200.0 mm 6 1/4 x 7 1/4 x 7 7/8 inch
Mass	Approx. 2.0 kg Approx. 4 lb 6.5 oz
Body Color	White/Black

Size of Screw Hole for Tripod	1/4-20UNC x1
Mountable Angle	< $\pm 15^\circ$
Ceiling Mount	Yes
Supplied Accessories	AC power adaptor (1) IR Remote Commander Unit (1) Ceiling bracket (2) Wire rope (1) Screw M3 x 8 (9) Screw M2.6 x 6 BLACK (1) HDMI cable fixing plate (1) Safety regulation (1) Download site information (1) Warranty (1)

## Notes

*1	CIZ = Clear Image Zoom
*2	Sony measurement conditions
*3	Available from V2.0 and later
*4	The values for dimensions are approximate

Related  
products



**REA-  
C1000  
Edge  
Analytics  
Appliance**

Edge Analytics  
Appliance



**BRC-AM7**

Premium PTZ Auto  
Framing Camera with  
AI Analytics, 4K 60p,  
20x optical zoom.  
High interoperability  
with other  
production systems

## Gallery



