

VPL-FHZ700L

7,000 lumens WUXGA 3LCD
Laser projector (colour
availability may vary by country)



Overview

The world's brightest* 3LCD projector comes with a long-lasting laser light source, and offers high WUXGA image quality, versatile installation options and lowered running costs.

The VPL-FHZ700L combines exceptional picture quality and brightness with the reliability, extended operating life and reduced running costs of laser projection.

Delivering crisp, brighter images with a class-leading 7,000 lumens brightness, the VPL-FHZ700L features a powerful, highly efficient laser light source that offers a nominal 20,000* hours operating time.

With no waiting time for lamps to warm up or cool down, switching on/off is virtually instantaneous. Together with the long-life 3LCD panel and advanced filter system, the laser light source cuts the need for regular maintenance visits. There's also a range of energy-saving features that contribute to a reduction in lifetime ownership costs compared with conventional projectors.

Its high brightness and minimal maintenance needs make the VPL-FHZ700L a compelling presentation choice in a wide range of applications – from boardrooms and lecture theatres to

museums, exhibitions and retail spaces.

Installer-friendly features like free-angle installation and edge blending also assist with integration into a wide range of corporate, educational, public sector and entertainment environments.

VPL-FHZ700L/W is a white model.

VPL-FHZ700L/B is a black model.

*1 As of March 2014

*2 With Auto Light Dimming feature enabled. Actual hours may vary depending on usage.

Features

Laser light source projector with Sony 3LCD BrightEra™ Panel Technology

The VPL-FHZ700L combines a highly efficient laser light source with Sony's advanced 3LCD BrightEra™ technology. This unique combination delivers exceptionally bright, pictures with excellent colour accuracy and stability, plus high efficiency and significantly greater durability for reduced total cost of ownership.

Clear, bright, punchy presentations in any lighting conditions

Add more detail, impact and realism to presentations with very high 7000 lumen brightness. Get your message across in large boardrooms, auditoriums or retail spaces even when ambient light levels are high.

Crisp, detail-packed WUXGA resolution images

See the finest detail in PC presentations, videos or multimedia signage with WUXGA (1920 x 1200) 16:10 resolution.

Up to 20,000* hours operation with virtually no

maintenance

The advanced laser light source offers a typical 20,000 hours operation without maintenance or replacement, reducing lifetime running costs compared with traditional projectors. 20,000 hours filter replacement cycles keep the projector in peak operating condition while reducing maintenance trips even further.

Wide range of Lens Shift, Zoom, Throw Ratio

Generous zoom, throw and lens shift adjustments give more flexibility for positioning the projector where you need it: close to ceilings, near the screen or even horizontally offset. Extend throw ratio even further with a choice of optional lenses.

360° free-angle installation capability

Enjoy supreme installation flexibility: position the projector freely at any angle – or its side or even upside down.

Connectivity via HDBaseT™

The projector allows simple connectivity using an HDBaseT digital interface, multi signal transmission system, providing a single cable, cost-effective, long-distance, and high-quality digital transmission solution.

Create super-size displays with Edge Blending

Seamlessly join accurately colour-matched images from multiple projectors, simplifying creation of stunning super-size displays for retail, corporate and live event applications.

Project onto non-flat surfaces with Image Warping

Easily correct image geometry for natural-looking projections – even on convex or concave surfaces. Corner and edge correction can be easily adjusted with the supplied remote and on-screen menu.

Advanced energy-saving features

Advanced light source and control technology enables robust

energy-saving features. Greater brightness control in Auto Dimming mode saves considerable energy when the projector is left on without being used. During projection, Auto Light output Mode automatically adjusts light output to suit the projected scene. When you need to mute the picture temporarily, light output can be completely deactivated to minimise energy consumption.

*1. With Auto Light Dimming feature enabled. Actual hours may vary depending on usage.

*2. HDBaseT™ and the HDBaseT Alliance logo are trademarks of the HDBaseT Alliance.

Specifications

Display System

Display System	3 LCD system
----------------	--------------

Display device

Size of effective display area	0.95" (24.1 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--------------------------------------------------------------

Number of pixels	6,912,000 (1920 x 1200 x 3) pixels
------------------	------------------------------------

Projection lens

Focus	Powered / Manual (Depend on lens)
-------	-----------------------------------

Zoom - Powered/Manual	Powered / Manual (Depend on lens)
--------------------------	-----------------------------------

Lens shift - Powered/Manual	Powered / Manual (Depend on lens)
--------------------------------	--------------------------------------

Light source

Type	Laser diode
------	-------------

Filter cleaning / replacement cycle (Max.) *1

Filter cleaning/ replacement cycle (Max.)	20000 H *2 (cleaning)
-------------------------------------------------	-----------------------

Screen size

Screen size	40" to 60" (1.02 m to 15.24 m) (measured diagonally) (Depend on lens)
-------------	-----------------------------------------------------------------------------

Light output

Lamp mode: High	7000 lm
-----------------	---------

Lamp mode: Standard	5600 lm
---------------------	---------

Color light output

	7000 lm
--	---------

Lamp mode: High

Lamp mode: Standard 5600 lm

Contrast ratio (full white / full black) *2

Contrast ratio (full white / full black) 8000:1

Displayable scanning frequency

Horizontal 14 kHz to 93 kHz

Vertical 47 Hz to 93 Hz

Display resolution

Computer signal input Maximum display resolution: WUXGA 1920 x 1200 dots*3

Video signal input NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, 1080/50p, 1080/24p

Color system

Color system NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60

Keystone correction (Max.)

Vertical +/- 30 degrees

Horizontal +/- 30 degrees

OSD language

OSD language 24-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)

INPUT OUTPUT (Computer/Video/Control)

INPUT A RGB / Y PB PR input connector: 5BNC (female)

INPUT B RGB input connector: Mini D-sub 15-pin (female)

INPUT C DVI-D input connector: DVI-D 24-pin (Single link), supported HDCP

INPUT D HDMI input connector: HDMI 19-pin, HDCP support

INPUT E	Optional adaptor slot (For Digital Interface Adaptor BKM-PJ10)*4
S VIDEO IN	S-video input connector: Mini DIN 4-pin
VIDEO IN	Video input connector: BNC
OUTPUT	Monitor output connector*5: Mini D-sub 15-pin (female)
REMOTE	RS-232C connector: D-sub 9-pin (female)
LAN	RJ-45, 10BASE-T/100BASE-TX
Control S	Control S input connector: Stereo mini jack, Plug in power DC 5V Control S output connector: Stereo mini jack

Acoustic noise

Lamp mode: Standard 33 dB

Operating temperature / Operating humidity

Operating temperature / Operating humidity
0°C to 40°C (32°F to 104°F) / 35% to 85% (no condensation)

Storage temperature / Storage humidity

Storage temperature / -10°C to +60°C (14°F to +140°F) /
Storage humidity 20% to 80% (no condensation)

Power Requirements

Power Requirements AC 100 V to 240 V, 5.0 A to 2.1 A,
50/60 Hz

Power Consumption

AC 100 V to 120 V Lamp mode: High: 497 W

AC 220 V to 240 V Lamp mode: High: 476 W

Power Consumption (Standby Mode)

AC 100 V to 120 V 0.1 W (when “Standby mode” is set
to “Low”)

AC 220 V to 240 V 0.5 W (when “Standby mode” is set
to “Low”)

Power Consumption (Networked Standby Mode)

12.2 W (LAN)

AC 100 V to 120 V	13.8 W (optional HDBaseT adaptor) 13.8 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")
-------------------	-------------------------------------------------------------------------------------------------------------------------------

AC 220 V to 240 V	8.4 W (LAN) 10.0 W (optional HDBaseT adaptor) 10.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")
-------------------	----------------------------------------------------------------------------------------------------------------------------------------------

Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	After about 2 minutes
-------------------------------------------------	-----------------------

Heat dissipation

AC 100 V to 120 V	1696 BTU/h
-------------------	------------

AC 220 V to 240 V	1624 BTU/h
-------------------	------------

Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Approx. 530 x 204 x 545 mm (20 7/8 x 8 1/32 x 21 15/32 inches)
-------------------------------------------------	-------------------------------------------------------------------

Mass

Mass	Approx. 22 kg (47 lb)
------	-----------------------

Supplied accessories

Remote commander	RM-PJ27
------------------	---------

Optional Accessories

Projection lenses	VPLL- 4008/Z4011/Z4015/Z4019/Z4025/Z4045/Z4007/ZM42/FM
----------------------	-----------------------------------------------------------

Projection lens adapter	PK-F500LA1, PK-F500LA2
-------------------------------	------------------------

Notes

*1	The figures are the expected maintenance time and not guaranteed. They will depend on the environment or how the projector is used.
----	-------------------------------------------------------------------------------------------------------------------------------------

*2	The value is average.
----	-----------------------

*3	Available for VESA Reduced Blanking signal.
*4	HDBaseT 3play (Video, Control, Ethernet)
*5	From INPUT A and INPUT B.

Gallery

