

## HDLA-1505/B

### HD Large Lens Adaptor



### Overview

The HDLA-1505/B allows operation of the HDC-1500 HD portable camera or HDC-3300 SuperMotion camera together with large studio/OB lenses and LCD viewfinders. Unlike traditional lens "build-up kits", the HDLA-1505/B provides a very simple one-touch cable-free mounting of the camera so that it can be quickly and easily converted from hand-held to tripod configuration.

#### Note

The HDLA-1505/B is finished in a dark grey body colour, the same as the HDC-1500 portable camera. If required, a pale coloured version, the HDLA-1505 is also available.

#### **One-touch instant docking mechanism**

The camera can be fitted quickly and easily into the adaptor. This unique mechanism allows the HDC-1500 to be attached and detached without removing the large lens.

#### **Quick mounting for portable camera head**

To provide efficient operation in studio or OB environments, the large lens adaptor has a unique design which allows the camera to be converted from hand-held to large lens configuration in just a few seconds.

#### **Cable-free operation with all connections contained in "hot shoe" mounting**

Utilizing a newly developed interlocking mechanism, power,

video, and control signals are passed on directly from the HDC-1500 to the HDLA-1505/B, without requiring additional cable connections.

Note that the HDVF-C730W viewfinder does require a conventional cable connection

### **Built-in teleprompter power supply**

Utility power (200-240V AC) is available from the large lens adaptor, when used in conjunction with the HDCU-1000 camera control unit

### **Same handling characteristic as full size camera**

All the control features and functionality traditionally associated with full size cameras are provided in this efficient operational package.

### **Compatible with HDVF-C730W colour LCD viewfinder**

The HDLA-1505 is specifically designed to allow the HDVF-C730W to be mounted on the rear of the camera body. The 7" CRT viewfinder, HDVF-700A, cannot be used with this lens adaptor

## Features

### **New low profile design with lower viewfinder height**

### **Direct docking mechanism**

## Related products



### **HDCU-5000**

Camera Control Unit

(CCU) for HDC-5500  
and HDC-3500/3100  
series system cameras

## Gallery

