

## LKRL-Z519

2D Projection Lens (1.90:1 to 4.00:1)



### Overview

#### **1.90x - 4.00x Zoom Lens**

Optional zoom lens for use with the SXR4 4K projector 1.90x to 4.00x zoom lens with memory feedback. This lens uses a feedback circuit that reports focus and zoom position to the projector. This allows the operator to preset and recall different lens settings from the projector function memories. This offers instant and automated screen sizing for video formats using different aspect ratios.

### Specifications

#### General

Operating temperature	0°C to +40°C
-----------------------	--------------

Storage temperature	-20°C to +60°C
---------------------	----------------

Operating humidity	0% to 90% (without condensation)
--------------------	----------------------------------

Storage humidity	0% to 90% (without condensation)
------------------	----------------------------------

Dimensions(W/H/L)	Approx. 256 x 315 x 413 mm(10 x 12.4 x 16.2 inches)
-------------------	---

Mass.

Approx. 13kg (28.6 lb)

---

## Gallery

