

VPL-FHZ120L

12,000 lm (13,100 lm center)
laser light source projector
(colour availability may vary by
country)



Overview

These high-brightness 3LCD laser projectors offer stunning image quality with excellent reliability. Ideal for auditoriums, lecture theatres, halls and larger venues, they're also great for teaching in brightly-lit classrooms.

A bright and vibrant image

Grab their attention – and keep it. The projectors' very high light output (12,000 lumens) ensures presentations with extra presence. You'll impress audiences in larger venues, from conference halls and lecture theatres to galleries, museums and visitor attractions.

Unforgettable images

Secure your competitive edge with visibly superior pictures – thanks to the combination of a newly developed 1-inch 3LCD panel and optical compensator with our unique Z-Phosphor Laser Light Source. It adds up to bright, beautiful images, bursting with fine detail and rich, sumptuous colours.

Even richer colours

The VPL-FHZ120L offers the ideal solution for auditoriums and conference halls, which require AV solutions for live performances and ceremonies. Additionally, the projector supports sRGB100% mode making it suitable for applications often found in exhibitions and museums which require precise

colour reproduction.

Made for flexible installation

Don't restrict your thinking. You'll appreciate the flexibility of industry-leading lens shift adjustment range and a wide choice of interchangeable lenses – giving more options to install the projector in any space, including classrooms and halls with high ceilings.

With normal lens shift

The projector requires a mounting bracket, which obscures the audience's view.

With wide lens shift

Lens shift gives greater installation flexibility, even in rooms with high ceilings.

Features

Deliver your message

Make sure your audience is always in the picture. Directly present HTML content – like corporate logos, images or information notices – over the network or from removable USB memory.

Beautifully consistent

Auto calibration maintains precise colour consistency over extended operating periods. It's especially valuable for environments like museums and galleries where you can't afford to compromise the artist's original vision.

Don't keep them waiting

Quick start-up saves time with every presentation. Switch on the VPL-FHZ120L and you're ready to start projecting at full brightness in moments. So you won't keep a room full of students waiting to see your point.

Instant recall

Memorise and instantly recall up to six projector settings for

image size, position and aspect ratio, saving valuable time for different environments and applications. (Requires optional VPLL-Z4111 lens)

Get closer to reality

Sony's advanced Reality Creation technology analyses the input signal right down to the pixel level. Powerful pattern matching enhances crispness of on-screen images and text without adding digital picture noise.

Specifications

Display System

Display System	3 LCD system
----------------	--------------

Display Device

Size of Effective Display Area	1" x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	---

Number of Pixels	6,912,000 (1920 x 1200 x 3) pixels
------------------	------------------------------------

Aspect Ratio	16:10
--------------	-------

Resolution	WUXGA (1920 x 1200 pixels)
------------	----------------------------

Projection Lens

Focus	Powered / Manual (Depend on lens)
-------	-----------------------------------

Zoom - Powered /	Powered / Manual (Depend on lens)
------------------	-----------------------------------

Manual	lens)
Zoom - Ratio	Depend on Lens
Throw Ratio	Depend on Lens
Lens Shift - Powered / Manual	Powered
Lens Shift - Range Vertical / Horizontal	Range Vertical: Depend on Lens Range Horizontal: Depend on Lens

Light Source

Type	Laser diode
------	-------------

Filter Replacement Cycle (Max.)

Filter Replacement Cycle (Max.)	10,000 H
---------------------------------	----------

Screen Size

Screen Size	Depend on Lens
-------------	----------------

Light Output *1

Mode: Standard	12,000lm *2
----------------	-------------

Mode: Standard

(Centre)	13,100 lm *3
----------	--------------

Mode: Middle	10,000 lm
--------------	-----------

Colour Light Output *1

Mode: Standard	12,000 lm
----------------	-----------

Mode: Middle	10,000 lm
--------------	-----------

Contrast Ratio *1

Contrast Ratio (full white / full black)	Contrast Ratio (full white / full black) : ∞ : 1
--	---

Colour Space

Colour Space	sRGB 100% (Picture mode: sRGB)
--------------	--------------------------------

Displayable Scanning Frequency

Horizontal	15 kHz to 92 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

Accepted Signal Resolution

Computer Signal Input	Maximum signal resolution: 1920 x
-----------------------	-----------------------------------

1200

Video Signal Input	480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i The following items are available for digital signal only; 1080/60p, 1080/50p, 1080/24p, 1080/30p *4
--------------------	--

Keystone Correction (Max.)

Horizontal	+/- 30 degrees
Vertical	+/- 30 degrees

INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: 5 BNC (female)
INPUT B	RGB input connector: Mini D-sub 15-pin (female)
INPUT C	DVI input connector: DVI-D 24-pin (single link), HDCP support HDCP: v1.4
INPUT D	HDMI input connector: HDMI 19-pin, HDCP support HDCP: v1.4

INPUT E	HDBaseT interface connector: RJ45, 3 play
INPUT F	Optional adaptor slot for 3G-SDI Input Adaptor (BKM-PJ20)
INPUT G	HTML Viewer
OUTPUT 1	Monitor output for Input A/Input B Connector: Mini D-sub 15-pin (female)
USB	Type-A x 1

INPUT OUTPUT (Others)

USB-1	Type-A x 1
-------	------------

Control Signal Input/Output

REMOTE	D-sub9pin male/RS232C
LAN	RJ45, 10BASE-T/100BASE-TX/1000BASE-T

Acoustic Noise *1

Light Output Mode: Standard	42dB
--------------------------------	------

Light Output Mode: 39dB
Middle

Operating Temperature / Operating Humidity

Operating Temperature / Operating Humidity 0°C to 45°C (32°F to 109°F) / 20% to 80% (no condensation)

Storage Temperature / Storage Humidity

Storage Temperature / Storage Humidity -10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)

Power Requirements

Power Requirements AC 100 V to 240 V, 10.8 A to 4.4 A, 50 Hz / 60 Hz

Power Consumption (Maximum)

AC 100 V to 120 V 1076 W

AC 220 V to 240 V 1033 W

Power Consumption (Standby Mode)

AC 100 V to 120 V 0.50W (when “Standby mode” is set)

to “Low”)

AC 220 V to 240 V

0.50W (when “Standby mode” is set to “Low”)

Power Consumption (Networked Standby Mode)

AC 100 V to 120 V

21.6W (LAN)
 26.5W (HDBT)
 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

AC 220 V to 240 V

21.3W (LAN)
 26.5W (HDBT)
 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

Dimensions (W x H x D) (without protrusions)

Dimensions (W x H x D) (without protrusions) Approx. 544 x 205 x 564 mm
 (21 13/32 x 8 1/16 x 22 7/32 inches)

Mass

Mass	Approx. 27 kg (58 lb)
------	-----------------------

Supplied Accessories

Remote Commander	RM-PJ30
------------------	---------

Projection Lens

Projection Lens	VPLL-4008, Z4111, Z4015, Z4019, Z4025, Z4045
-----------------	---

Optional Projection Lens

VPLL-4008	Throw Ratio: 1:00:1 Lens Shift - Range Vertical: +/-32% Lens Shift - Range Horizontal: +/-15%
-----------	--

VPLL-Z4111	Throw Ratio: 1:30:1 to 1:96:1 Lens Shift - Range Vertical: +/-99% Lens Shift - Range Horizontal: +/-51%
------------	--

VPLL-Z4015	Throw Ratio: 1:85:1 to 2:44:1 Lens Shift - Range Vertical: +/-98% Lens Shift - Range Horizontal: +/-51%
------------	--

	Throw Ratio: 2:41:1 to 3:07:1
--	-------------------------------

VPLL-Z4019	<p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p>
VPLL-Z4025	<p>Throw Ratio: 3:02:1 to 5:58:1</p> <p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p>
VPLL-Z4045	<p>Throw Ratio: 5.56:1 to 7.5:1</p> <p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p>

Notes

*1 The figures are approximate. They vary depending on the environment or how the projector is used.

*2 The value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary depending on use conditions and environments.

*3

The value is light output measured at center area of screen in Standard mode, and average of all products shipped.

*4

When using BKM-PJ20

Gallery

