

## VPL-FHZ65

6,000 lumens WUXGA laser light source projector (colour availability may vary by country)

### Overview

#### **Bright, beautiful images with low running costs, minimal maintenance and flexible installation**

The VPL-FHZ65 laser projector is ideal for a wide range of business, education and entertainment applications. The powerful Z-Phosphor laser light source is teamed with Sony's advanced BrightEra 3LCD projection engine to deliver extremely bright, detail-packed WUXGA resolution images with generous 6000 lumens brightness and rich, stable colours. Constant Bright Maintains the same brightness throughout the 20,000 hours recommended life span.

The laser light source allows up to 20,000 hours\* of virtually zero maintenance operation without the worry of sudden lamp failures. A new automated filter system cuts the hassle of regular dust cleaning. Near-zero maintenance needs are complemented by a range of energy-saving feature, significantly driving down total lifetime ownership costs.

Offering a stylish new blend-in design, tidy cable management and low fan noise, the VPL-FHZ65 fits smoothly into almost any environment – from academic institutions, corporate, medical training and public sector organisations to visitor attractions and retail spaces. Seamlessly blend images from multiple projectors to create super-sized displays, or project accurately proportioned images onto angled or curved surfaces. Mount the projector at any angle, even on its side or upside down. Set-up's easier than ever with a friendly new installation menu.

VPL-FHZ65/W is a white model.

VPL-FHZ65/B is a black model.

**Black and lensless models available in Europe; please check for local availability.**

\*Actual hours may vary depending on usage environment.

## Features

### **Very high image quality with Sony's advanced BrightEra 3LCD projection engine and Z-Phosphor laser light source**

The Z-Phosphor laser light source is coupled with Sony's acclaimed BrightEra 3LCD projection engine to ensure high 6000 lumen image brightness with vivid, natural colour reproduction.

### **Constant Brightness**

Constant Bright Maintains the same brightness throughout the 20,000 hours recommended life span.

### **Advanced picture refinement technologies**

Picture quality is boosted by advanced processing featured on Sony home cinema projectors. Reality Creation uses a powerful pattern-matching database to optimise every pixel. Contrast Enhancer actively analyses and refines dark and light image areas for sparkling highlights and rich, deep blacks.

### **Crisp, detail-packed WUXGA resolution images**

See the finest detail in PC presentations, videos or multimedia signage with WUXGA (1920 x 1200) 16:10 resolution.

### **Up to 20,000 hours\* operation with virtually no maintenance**

The advanced laser light source offers up to 20,000 hours\*

operation without lamp exchange, reducing lifetime running costs compared with traditional projectors.

\*Actual hours may vary depending on usage environment.

### **Hassle-free automatic filter cleaning**

Focus on great-looking images instead of arduous maintenance tasks: new automated filter cleaning system removes dust every 100 hours.

### **Energy saving features**

Reduce running costs even further with convenient energy-saving features: Picture Mute and Auto Dimming.

### **Save time with every presentation**

Quick power On/Off dramatically cuts warm-up time after switch-on before you can start presenting at full brightness.

### **360° free-angle installation capability**

Enjoy greater installation flexibility: position the projector freely at any angle – or its side or even upside down.

### **Powered Wide Lens Shift**

Generous lens shift adjustments give more flexibility for positioning the projector where you need it: close to ceilings or even horizontally offset.

### **Included powered standard zoom lens plus wide choice of lens options**

Installation flexibility is increased by a wide range of compatible lens options to suit virtually any size of room and throw requirements. New quick-release bayonet mount simplifies quick lens exchange.

### **Supports HDBaseT**

Simpler, more cost-effective installation and connectivity with digital transmission of HD video, audio and networking/control

over a single Ethernet cable.

### **Create super-size displays with Edge Blending**

Seamlessly join accurately colour-matched images from multiple projectors, simplifying creation of stunning super-size displays for corporate and education.

### **Project onto non-flat surfaces with Image Warping**

Easily correct image geometry for natural-looking projections – even on convex or concave surfaces. Corner and edge correction can be easily adjusted with the supplied remote and on-screen menu.

### **Quiet operation**

Low fan noise ensures discreet, unobtrusive operation in quiet environments from museums and galleries to lecture theatres.

### **Slim, attractive new blend-in design**

The slim, stylish case design features a flat top surface that blends in discreetly when the projector is ceiling mounted. The clean appearance is accentuated by a new terminal cover that reduces cable clutter.

### **Picture Mode**

New Picture Mode ensures great-looking pictures in any presentation conditions. Select Standard, Dynamic, Brightness Priority or Multi Screen mode for optimised image quality, with any source and in every room.

### **Simple set-up with friendly new Installation menu**

Easily adjust projector settings with remote commander, including warping and edge blending.

### **Project Side by Side**

Project images from two inputs at the same time: ideal for applications such as video conferencing and medical training where two images need to be seen simultaneously.

## Specifications

### Display system

Display system	3 LCD system
----------------	--------------

### Display device

Size of effective display area	0.76" (19 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--

Number of pixels	6,912,000 (1920 x 1200 x 3) pixels
------------------	------------------------------------

### Projection lens \*1

Focus	Powered
-------	---------

Zoom - Powered/Manual	Powered
-----------------------	---------

Zoom - Ratio	Approx. x 1.6
--------------	---------------

Throw ratio	1.39:1 to 2.23:1
-------------	------------------

Lens shift - Powered/Manual	Powered
-----------------------------	---------

Lens shift - Range Vertical	-5%, +60%
-----------------------------	-----------

Lens shift - Range Horizontal	+/- 32%
-------------------------------	---------

## Light source

Type	Laser diode
------	-------------

---

## Filter cleaning / replacement cycle (Max.)\*2

Filter cleaning / replacement cycle (Max.)	20000 H (service maintenance)
--	-------------------------------

---

## Screen size

Screen size	40" to 600" (1.02 m to 15.24 m) (measured diagonally)
-------------	--

---

## Light output

Mode: High	6000 lm
------------	---------

---

Mode: Standard	4000 lm
----------------	---------

---

## Color light output

Mode: High	6000 lm
------------	---------

---

Mode: Standard	4000 lm
----------------	---------

---

## Contrast ratio (full white / full black) \*3

Contrast ratio (full	
----------------------	--

---

Contrast ratio (full white / full black) 10000:1

---

## Displayable scanning frequency

Horizontal 15 kHz to 92 kHz

---

Vertical 48 Hz to 92 Hz

---

## Display resolution

Computer signal input Maximum display resolution: 1920 x 1200 dots \*4

---

Video signal input NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i  
The following items are available for digital signal (HDMI input) only; 1080/60P, 1080/50p, 1080/24p

---

## Color system

Color system NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60

---

## Keystone correction (Max.)

Horizontal +/- 30 degrees

---

Vertical

+/- 30 degrees

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	<p>RGB / Y PB PR input connector: Mini D-sub 15 pin (female)</p> <p>Audio input connector: Stereo mini jack</p>
INPUT B	<p>DVI input connector: DVI-D 24-pin (single link), HDCP support</p> <p>Audio input connector: Shared with INPUT A</p>
INPUT C	<p>HDMI input connector: HDMI 19-pin, HDCP support</p> <p>Audio input connector: HDMI audio support</p>
INPUT D	<p>HDBaseT interface connector: RJ45, 4 play (Video, Audio, LAN, Control)</p>
VIDEO IN	<p>Video input connector: BNC</p> <p>Audio input connector: Shared with input A</p>
OUTPUT A	<p>Monitor output for Input A</p> <p>Connector: Mini D-sub 15-pin (female)</p>



	Audio output connector: Stereo mini jack
OUTPUT B	Monitor output for Input B Connector: DVI-D 24-pin (single link), HDCP not supported Audio output, Monitor out connector: Stereo mini jack
REMOTE	D-sub 9-pin (male) / RS232C
LAN	RJ45, 10BASE-T/100BASE-TX
IR (Control S)	Stereo mini jack, Plug in power DC5V

## Acoustic Noise

Lamp mode: Standard 28 dB

## Operating temperature / Operating humidity

Operating temperature / Operating humidity 0°C to 40°C (32°F to 104°F) / 20% to 80% (no condensation)

## Storage temperature / Storage humidity

Storage temperature / -10°C to +60°C (14°F to +140°F) /

Storage humidity	20% to 80% (no condensation)
------------------	------------------------------

---

## Power requirements

Power requirements	AC 100 V to 240 V, 5.5 A to 2.3 A, 50 Hz / 60 Hz
--------------------	--

---

## Power consumption

AC 100 V to 120 V	Mode: High: 509 W
-------------------	-------------------

---

AC 220 V to 240 V	Mode: High: 492 W
-------------------	-------------------

---

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5W (when "Standby mode" is set to "Low")
-------------------	--

---

AC 220 V to 240 V	0.5W (when "Standby mode" is set to "Low")
-------------------	--

---

## Power Consumption (Networked Standby Mode)

	15.0 W (LAN)
	15.0 W (HDBaseT)
AC 100 V to 120 V	15.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to

---

"Standard")

AC 220 V to 240 V

13.3 W (LAN)  
 13.3 W (HDBaseT)  
 13.3 W (All Terminals and  
 Networks Connected) (when  
 "Standby Mode" is set to  
 "Standard")

## Standby Mode / Networked Standby Mode Activated

Standby Mode /  
 Networked Standby Mode Activated      Approx. 10 Minutes

## Dimensions (W x H x D)

Dimensions (W x H x D)      460 x 169 x 515 mm  
 (without protrusions)      18 1/8 x 6 21/32 x 20 9/32 inches

## Mass

Mass      16 kg (34 lb)

## Supplied accessories

Remote commander      RM-PJ27

## Optional accessories

Projection Lens	VPLL-3007 / Z3009 / Z3024 / Z3032
-----------------	-----------------------------------

---

## Notes

*1	With supplied standard lens
----	-----------------------------

---

*2	This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used.
----	---

---

*3	The value is average.
----	-----------------------

---

*4	Available for VESA Reduced Blanking signal.
----	---

---