

## VPL-FHZ75

6,500 lm (7,000 lm center)  
WUXGA laser light source  
projector



### Overview

#### **With advanced image technologies for high contrast presentations and installation-friendly features**

The compact, elegantly styled VPL-FHZ75 laser projector showcases cutting-edge Sony picture innovations and installation-friendly features - making it ideal for high brightness projection applications in midsize corporate, education and public environments.

The projector's long-lasting laser light source and newly-developed 0.76-inch 3LCD panel with incorporated optical compensator are augmented by powerful Reality Creation and colour processing technologies by Sony. This ensures exceptionally high-contrast images with WUXGA resolution, true-to-life colour and very high 6,500 lumens brightness - ideal for delivering lectures and presentations with extra audience engagement.

Leveraging its long-term experience in laser projector development and analysis, Sony's Intelligent Setting function simplifies installation, offering four pre-sets that adjust brightness, cooling system, colour and other projector settings for optimal performance in meeting/classrooms, museums, entertainment venues and multi-screen setups.

With its compact 'blend-in' design and widest vertical lens shift range in its class, the VPL-FHZ75 is ideal for installation even in limited spaces, while extra flexibility's provided with accurately-proportioned projection onto angled surfaces.

## Features

### **High contrast, very high quality 6,500 lumen images**

The laser is complemented by a newly-developed 0.76-inch LCD panel with incorporated optical compensator. Combined with powerful signal processing technology, this ensures vivid images with crisp detail,  $\infty$ :1 contrast and natural, accurate colour reproduction.

### **Advanced picture refinement technologies**

Picture quality is boosted by Sony's unique super resolution Reality Creation technology which uses a powerful pattern-matching database to optimise lower-resolution images, enhancing image clarity without increasing digital picture noise.

### **Intelligent Settings**

Leveraging its long-term experience in laser projector development and analysis, Sony's Intelligent Settings offer four presets, optimising brightness, cooling system and other projector settings to suit all usage environments - simplifying installation for busy system integrators.

### **Wide Lens Shift**

The industry's widest lens shift\* capability of Vertical +70% gives greater flexibility for positioning the projector, and ensures that presenters or visitors aren't distracted by the projector's light source.

\*In the range of 5000-6500 lm. As of 5th February 2019, according to Sony research.

## **Included powered standard zoom lens plus wide choice of lens options**

Installation flexibility is increased by a wide range of compatible lens options to suit virtually any size of room and throw requirements. New quick-release bayonet mount simplifies lens exchange.

## **Constant Brightness**

Constant Bright maintains the same brightness throughout the 20,000 hours recommended lifespan.

## **Slim, attractive blend-in design**

The slim, stylish body design features a flat top surface that blends in discreetly when the projector is ceiling mounted. The clean appearance is accentuated by a new terminal cover that reduces cable clutter.

## **Up to 20,000 hours\* operation with virtually no maintenance**

The advanced laser light source offers up to 20,000 hours\* operation without lamp exchange, reducing lifetime running costs compared with traditional projectors.

\*Actual hours may vary depending on usage environment.

## **Hassle-free automatic filter cleaning**

Focus on great-looking images instead of arduous maintenance tasks: automated filter cleaning system removes dust every 100 hours.

## **Create super-size displays with Edge Blending**

Seamlessly join accurately colour-matched images from multiple projectors, simplifying creation of stunning super-size displays for corporate and education.

## **Built-in Auto Calibration**

After extended periods, colour can be automatically calibrated to the original factory condition. There's no need for extra

calibration equipment or cameras; a built-in colour sensor stores all the necessary information.

## Network and control

The projector is ideal for integration in AV environments with leading networked control, monitoring and management systems such as Crestron Connected™ and newly added Extron® XTP™ Systems.\*

\*Extron and XTP Systems are trademarks of RGB Systems Inc.

## Specifications

### Display system

Display system	3 LCD system
----------------	--------------

### Display device

Size of effective display area	New LCD panel 0.76" (19 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--

Number of pixels	6,912,000 (1920 x 1200 x 3) pixels
------------------	------------------------------------

### Projection lens \*1

Focus	Powered
-------	---------

Zoom - Powered/Manual	Powered
--------------------------	---------

Zoom - Ratio	Approx. x 1.6
--------------	---------------

Throw ratio	1.39:1 to 2.23:1
-------------	------------------

Lens shift - Powered/Manual	Powered
--------------------------------	---------

Lens shift - Range Vertical	-5%, +70%
--------------------------------	-----------

Lens shift - Range Horizontal	+/- 32%
----------------------------------	---------

## Light source

Type	Laser diode
------	-------------

## Filter cleaning / replacement cycle (Max.)\*2

Filter cleaning / replacement cycle (Max.)	20000 H (service maintenance)
--	-------------------------------

## Screen size

Screen size	40" to 600" (1.02 m to 15.24 m) (measured diagonally)
-------------	--

## Light output \*3

Mode: Standard	6500lm *4 / 7000lm (Center)*5
----------------	-------------------------------

Mode: Middle	5200lm
--------------	--------

Mode: Low	-
-----------	---

## Colour light output \*3

Mode: Standard	6500lm
----------------	--------

Mode: Middle	5200lm
--------------	--------

Mode: Low	-
-----------	---

## Contrast ratio (full white / full black) \*3

Contrast ratio (full white / full black)	$\infty$ :1
--	-------------

## Displayable scanning frequency

Horizontal	15 kHz to 92 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

## Accepted signal resolution

Computer signal input	Maximum signal resolution: 1920 x 1200 *6
-----------------------	---

NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p,

Video signal input	720/50p, 1080/60i, 1080/50i The following items are available for digital signal (HDMI input) only; 1080/60P, 1080/50p, 1080/24p
--------------------	---

---

## Colour system

Colour system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60
---------------	---

---

## Keystone correction (Max.)

Horizontal	+/- 30 degrees
------------	----------------

---

Vertical	+/- 30 degrees
----------	----------------

---

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15 pin (female) Audio input connector: Stereo mini jack
---------	--

---

INPUT B	DVI input connector: DVI-D 24-pin (single link), HDCP support Audio input connector: Shared with INPUT A
---------	---

---

	HDMI input connector: HDMI 19-
--	--------------------------------

---

INPUT C	pin, HDCP support Audio input connector: HDMI audio support
INPUT D	HDBaseT interface connector: RJ45, 4 play (Video, Audio, LAN, Control)
VIDEO IN	Video input connector: BNC Audio input connector: Shared with input A
OUTPUT A	Monitor output for Input A Connector: Mini D-sub 15-pin (female) Audio output connector: Stereo mini jack
OUTPUT B	Monitor output for Input B Connector: DVI-D 24-pin (single link), HDCP not supported Audio output, Monitor out connector: Stereo mini jack
REMOTE	D-sub 9-pin (male) / RS232C
LAN	RJ45, 10BASE-T/100BASE-TX
IR (Control S)	Stereo mini jack, Plug in power DC5V



## Acoustic Noise \*3

Lamp mode : Middle      36 dB

---

## Operating temperature / Operating humidity

Operating temperature /  
Operating humidity      0°C to 40°C (32°F to 104°F) / 20% to 80% (no condensation)

---

## Storage temperature / Storage humidity

Storage temperature /  
Storage humidity      -10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)

---

## Power requirements

Power requirements      AC 100 V to 240 V, 5.4 A to 2.2 A, 50 Hz / 60 Hz

---

## Power consumption

AC 100 V to 120 V      Mode: Standard: 537 W

---

AC 220 V to 240 V      Mode: Standard: 518 W

---

## Power consumption (Standby Mode)

AC 100 V to 120 V      0.5W (when “Standby mode” is set)

---

AC 100 V to 120 V	to “Low”
AC 220 V to 240 V	0.5W (when “Standby mode” is set to “Low”)

## Power consumption (Networked Standby Mode)

AC 100 V to 120 V	16.0 W (LAN) 20.7 W (HDBaseT) 20.7 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")
AC 220 V to 240 V	13.3 W (LAN) 18.7 W (HDBaseT) 18.7 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

## Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	Approx. 10 Minutes
---	--------------------

## Heat dissipation

---

AC 100 V to 120 V	1833 BTU/h
-------------------	------------

---

AC 220 V to 240 V	1768 BTU/h
-------------------	------------

---

## Dimensions (W x H x D)

Dimensions (W x H x D)	460 x 169 x 515 mm
(without protrusions)	18 1/8 x 6 21/32 x 20 9/32 inches

---

## Mass

Mass	Approx. 16 kg (34 lb)
------	-----------------------

---

## Optional accessories

Projection Lens	VPLL-3003 / 3007 / Z3009 / Z3010 / Z3024 / Z3032
-----------------	--

---

## Notes

*1	With supplied standard lens
----	-----------------------------

---

*2	This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used.
----	---

---

The figures are approximate. They

\*3 vary depending on the environment or how the projector is used.

---

\*4 The value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary depending on use conditions and environments.

---

\*5 The value is light output measured at centre area of screen in Standard mode, and average of all products shipped.

---

\*6 Available for VESA Reduced Blanking signal.

---

## Gallery



