

FWA-CE100

Full HD USB camera with microphone for Professional Displays



Overview

Video conferencing made elegantly simple

The FWA-CE100 USB camera can be mounted easily on Sony Professional Displays, capturing finely-detailed Full HD video and crisp, highly directional sound in meeting rooms and huddle spaces.

Combined with and optional WQ-BM1 Meeting Room software (NB: availability may vary by region), the FWA-CE100 offers a highly cost effective all-in-one video conferencing solution for corporate applications.

Features

High quality Full HD images, wide field of view

Enjoy crisply detailed video conferences in smooth Full HD. The camera's wide field of view (77.5 degrees horizontal) allows every participant to be seen around the meeting table.

Crisp, clear speech quality

High quality dual unidirectional microphones capture speech and other room sounds directly, with excellent clarity and minimised pick-up of reflected sound.

Simple video conferencing solution

Combining the FWA-CE100 with a display and optional

WQ-BM1 Meeting Room software creates a cost-effective 'all in one' video conferencing solution, with no additional hardware required. Please note that WQ-BM1 availability may vary by region.

Specifications

Specifications

| | |
|------------------------|--|
| Image Sensor | Sony IMX208 Exmor R™ CMOS Sensor |
| Resolution | 1920x1080, 1280x720, 960x540, 768x480, 640x480, 640x360, 480x270 |
| Frame Rate | 30fps - 5fps |
| Field of View | 77.5 |
| Lens | F/2.0 |
| Focus | Fixed |
| Video Compression | H.264 & VP8 up to 16Mbps |
| Microphone | Two unidirectional microphones |
| Interface | USB 2.0 High Speed, UVC 1.1 |
| Width x Height x Depth | 80.0 mm x 25.6 mm x 70.1mm |
| Weight | 80g (144g with carton) |
| Cable Length | 1.5m |
| Operating | 0°C - 40°C |

temperature

Power Supply

DC 5 V, 500 mA (USB Bus Power)

Supported OS

BRAVIA Android TV 8.0 or later

Compatible Products

Compatible only with BZ35F series BRAVIA Professional Displays

Gallery

