

## BRBK-SF1

**Allows transmission of HD signal up to 2,000 metres with BRU-SF10 HD optical multiplex unit**

The BRBK-SF1 interface card is designed for use for use with the BRC-H900P Full-HD robotic camera and the BRC-Z330 HD robotic camera. The combined use of this card, CCFC-S200200m single-mode optical fibre cable segments and BRU-SF10 HD optical multiplex unit allows up to 2,000 metres (6,562 feet) transmission of camera images, external video syncsignals, 2 analogue audio channels and control signals via optical fibre cable.



