

FWD-65X85G

65" BRAVIA 4K Ultra HD,
HDR, LED Professional
Display



Overview

Impressive 4K HDR images and powerful sound plus slim, sleek styling

Add presence to all your visual communication with the FWD-65X85G 65" BRAVIA Professional Display that combines bright, beautiful 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Optimised for professional applications, the BRAVIA FWD-65X85G features Sony's advanced 4K HDR Processor X1 for richly coloured, high-contrast 4K HDR images, while 4K X-Reality PRO upscales lower-resolution images closer to true 4K quality.

The display's clean, minimal design keeps your audience focused on what really matters. And Sony's Acoustic Multi-Audio™ system and Sound-from-Picture Reality™ ensures an immersive audio-visual experience.

It's easy to create attractive digital signage, mixing media files and online content with no need for additional player hardware. There's also a wide range of APIs (Application Programming Interface) options to enable remote control/monitoring and integration with

external systems.

Android TV makes your professional display experience even smarter, allowing you to search apps and content with easy hands-free voice searches.

Integration in corporate environments is simplified by Pro mode that allows easy customisation of display settings to suit different applications.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

Beautifully realistic 4K HDR images

Our 4K HDR Processor X1™ features Object-based HDR remaster, Super Bit Mapping HDR and Dynamic Contrast Enhancer. You'll appreciate the difference with enhanced depth, more realistic textures and pure, natural colours at higher brightness levels.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

More colour with TRILUMINOS Display

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of richer, more lifelike hues and tones.

Smoother movement

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

Optimised for professional use

The FWD-65X85G meets the needs of today's business and educational environments, with flexible installation options plus wired or wireless network connection and serial communication control.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage, with no extra hardware or prior training needed. Combine graphics, text, 4K video and live web content to create attractive signage in minutes.

Pictures and sound in perfect harmony

Sony's Acoustic Multi-Audio™ system combines two sound positioning tweeters in the rear of the display with the bass reflex speakers for Sound-from-Picture Reality™. Action and sound are precisely aligned for even more immersive viewing.

Do more with Android TV

Discover a world of apps and online content powered by Android TV. Use Voice Search to find content easily with no typing.

Flexible mounting and installation

BRAVIA Professional Displays offer flexible mounting options with VESA standard mounting for easy integration into a wide range of environments.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy them easily to multiple displays via USB flash

memory.

Specifications

TV System

Tuner	DVB-T/T2
Number of tuners	1 (Digital / Analog)

Display features

Dimming type	Frame Dimming
Display device	LCD
Backlight type	Edge LED

Video specs

Wide Mode	Wide zoom / Normal / Full / Zoom / 14:9
4:3 Default	Yes
Video Processing	4K X-Reality PRO
Motionflow	Motionflow XR 200Hz (Native 100Hz), Auto mode
Compatible with HDR	Yes (HDR10, HLG, Dolby Vision)
Video Signal	4096 x 2160p (24, 50, 60Hz), 3840 x 2160p (24, 25, 30, 50, 60Hz), 1080p (30, 50, 60Hz), 1080/24p, 1080i (50, 60Hz), 720p (30, 50, 60Hz), 720/24p,

576p, 480p

Audio specs

Speaker position Side Back + Down Firing

Audio Power Output 10W + 10W

Network specs

Wi-Fi direct Yes

Wi-Fi Certified Yes

DLNA Home Network Client, Home Network Renderer

Miracast (screen mirroring) Yes (only for B2B purpose)

Firmware update Yes

Internet Browser Vewd

Wireless LAN Integrated

Convenience features

USB Play (contents) MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV, AVCHD):MPEG2, AVC / MP4 (XAVC S):AVC, MPEG4, HEVC / AVI:Xvid, MotionJpeg / ASF (WMV):VC1 / MOV:AVC, MPEG4, MotionJpeg /

MKV:Xvid, AVC, MPEG4, VP8.
HEVC / WEBM:VP8 /
3GPP:MPEG4, AVC / MP3 / ASF
(WMA) / WAV / MP4AAC / FLAC
/ JPEG

On screen clock	Yes
Sleep timer	Yes
On/Off timer	Yes
Google Cast	Yes

Inputs and outputs

HDCP	HDCP 2.3 (for HDMI 1 / 2 / 3 / 4)
RF Connection Input(s)	1 (Side)
Composite Video Input(s)	1 (Rear)
Component Video (Y / Pb / Pr) Input(s)	1 (Rear / Hybrid with Composite Video Input)
HDMI™ Connection(s) (Total)	4 (3 Side, 1 Rear)
Digital Audio Output(s)	1 (Rear)
USB	3 (Side)
Ethernet Connection(s)	1 (Side)

Design features

Finish (Surface Color)	Black
Table Top Stand	Separate (assembly required)
VESA® Hole Spacing Compatible	Yes
VESA® Hole Pitch	300 x 300 mm

Eco and energy saving

Screen size (measured diagonally)	65" (64.5")
Power Consumption (Rated / Standard)	199W
Annual Power Consumption	473 kWh / Year
Power Consumption (in Standby)	0.5 W
Power Requirements	AC 110-240 V
Power Saving Mode / Back Light Off Mode	Yes

Dynamic Backlight Control	Yes
---------------------------	-----

Light Sensor	Yes
--------------	-----

AC Power Input	1 (REAR)
----------------	----------

Measurements

Display Only (W x H x D) (Approx.)	Approx. 1450 x 836 x 52 (14.1) mm
------------------------------------	-----------------------------------

Display with Stand (W x H x D) (Approx.)	Approx. 1450 x 899 x 316 mm
--	-----------------------------

Package Carton (W x H x D) (Approx.)	Approx. 1567 x 949 x 181 mm
--------------------------------------	-----------------------------

Weight

Display Only	25.3 kg
--------------	---------

Display with Stand	26.3 kg
--------------------	---------

Package Carton	35 kg
----------------	-------

Display specifications

Viewing angle (Right / Left)	178 (89 / 89) degree
-------------------------------	----------------------

Viewing angle (Up / Down)	178 (89 / 89) degree
---------------------------	----------------------

Display resolution	QFHD
--------------------	------

Aspect ratio	16:9
OS	Android 8.0 Oreo

Signage specs

Easy HTML5 Signage embedded	Yes
-----------------------------	-----

Multicast / IPTV	Yes
------------------	-----

Control specs

Hotel Mode Pro	Yes
----------------	-----

IP Control	Yes
------------	-----

HDMI auto wake-up	Yes
-------------------	-----

Gallery

