


# File Manager2

\*Please contact your local sales representative for details.



## Overview

### Control for Optical Disc Archive PetaSite scalable library and ODS-L10 mini robotic library

After File Manager2 software is installed on a host computer, all operations are controlled with a web-based GUI from each client computer. It uses a simple Drag & Drop operation to archive and retrieve files and provides the opportunity for the user to add text metadata when archiving files.

File Manager2 software gives you the ability to archive/retrieve your content to/from ODS USB Drive series, ODS-L10 and ODS-L30M from a PC.

In addition, offline media searching is possible because FM2 records the file information to its own database.

## Features

### Control all library operations with a simple web-based GUI

After the File Manager2 software is installed on a host computer, all operations can be controlled with a web-based GUI, from each client computer. Using a simple drag & drop functionality to archive and retrieve files, File Manager2 also provides the opportunity for the user to add text metadata when archiving files.

### Categorisation by cartridge

In the case of ODS-L10, it contains up to 10 cartridges as online (total 15TB with ten ODC-1500R), and you can use different cartridges per category or user. Placeholder to archive together multiple files from different folders and add text metadata when archiving files.

### Support all line-ups

File Manager2 can control both USB type standalone drive (ODS-D55U or ODS-D77U) and libraries (ODS-L10 or ODS-L30M).

### Simplest solution for shelf archive

File Manager2 is able to search your cartridge even it's on shelves, as well as online cartridge in ODS-L10 or ODS-L30M.

## Specifications

| File Manager mode |                                                                                                                                      |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Processor         | CPU Intel Core i5 3 GHz or higher                                                                                                    |
| Memory            | 8 GB                                                                                                                                 |
| HDD capacity      | 200 GB<br>(Additional capacity of 4 TB/drive is required if archiving files from the local HDD or retrieving files to the local HDD) |

## File Manager mode

|           |                                                                                                                                                                                                                                                                                                                                                                                                                 |
|-----------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| OS        | <b>ODS-L10 or USB drive unit connection:</b><br>Windows 10 64-bit<br><b>ODS-L30M connection:</b><br>Windows Server 2012<br>Windows Server 2012 R2<br>Windows Server 2016                                                                                                                                                                                                                                        |
| Interface | <b>ODS-L10 connection:</b><br>Ethernet × 2 ports (for PC client connection and ODS-L10 connection) USB 3.0 ports (one for each drive)<br><b>ODS-L30M connection:</b><br>Ethernet × 1 port (for PC client connection and ODS-L30M connection) Fibre Channel HBA (Host Bus Adapter)<br><b>Drive unit direct connection:</b><br>Ethernet × 1 port (for PC client connection)<br>USB 3.0 ports (one for each drive) |

## File Server mode

|              |                                                                      |
|--------------|----------------------------------------------------------------------|
| Processor    | CPU Intel Core i5 3 GHz or higher                                    |
| Memory       | 8 GB                                                                 |
| HDD capacity | 200 GB + 4 TB/drive                                                  |
| OS           | Windows Server 2012<br>Windows Server 2012 R2<br>Windows Server 2016 |
| Interface    | Same as File Manager mode                                            |

Related products



**ODS-D55U**

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



**ODS-D77UA**

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.



**ODS-L30M**

\*Please contact your local sales representative for details.



**ODS-L60E**

\*Please contact your local sales representative for details.



**ODS-L100E**

\*Please contact your local sales representative for details.



**Optical Disc Archive Software (Driver)**

\*Please contact your local sales representative for details.




**ODS-D280U**

Optical Disc Archive standalone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



**ODS-D280F**

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



**File Server mode License for FM2**

\*Please contact your local sales representative for details.



**ODS-D380F**

\*Please contact your local sales representative for details.



**ODS-D380U**

\*Please contact your local sales representative for details.

Gallery

