

## PSS-650

### Projector Ceiling Bracket for Installation



#### Overview

#### Projector Ceiling Bracket for Installation

#### Specifications

##### Adjustable range

Up/down position	300~375mm / 11 13/16~14 3/4 inches 475~625 mm / 18 11/16~24 19/32 inches (with Supplied extension pole) (25mm pitch adjustment)
Horizontal angle of rotation	$\pm 10$ deg
Left/right tilt angle	$\pm 5$ deg (Fine adjustment function with adjustment knob)
Up/down tilt angle	$\pm 5$ deg (Fine adjustment function with adjustment knob)
Front/back position	$\pm 50$ mm / $\pm 1$ 31/32 inches (Fine adjustment function with

adjustment knob)

Left/right position

$\pm 25$  mm /  $\pm 31/32$  inch (Fine adjustment function with adjustment knob)

## Dimensions (W x H x D)

Dimensions (W x H x D)

299 x Height\* x 453.5 mm / 11 25/32 x H x 17 27/32 inches

\*Height: 300~375mm / 11 13/16~

14 3/4 inches

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

## Dimensions (W x H x D) \*without protrusions (Adjustment knob)

Dimensions (W x H x D)

246 x Height\* x 322 mm / 9 11/16 x H x 12 11/16 inches

\*without protrusions

\*Height : 300~375mm / 11 13/16

~14 3/4 inches

(Adjustment knob)

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

## Mass

Mass	Approx. 8.6 kg / 19 lb
------	------------------------

---

Maximum load

Maximum load	30 kg / 66 lb
--------------	---------------

---

Optional accessories

Optional accessories	PSS-650P
----------------------	----------

---

Color

Color	Black
-------	-------

---

## Gallery

