

RM-30BP

Remote Commander



Overview

The RM-30BP is the successor to the RM-1000BP, the industry's first comprehensive, multifunctional remote commander.

Ideal for freelancers and small-budget productions, the lightweight remote can be handheld, placed on a table or attached to a tripod arm for operation. The RM-30BP can control most camera functions including:

- Lens control: one push auto / manual focus, iris and zoom control
- Camera control: recording / display functions, shutter speed, white balance - including six assignable buttons
- Playback and multi camera control (up to 3 cameras)

The RM-30BP is compatible with a wide-range of Sony camcorders, including PXW-FX9 and ILME-FX6. Please consult Resources section for latest Compatibility Notes PDF.

Specifications

Notes

Specifications are tentative and subject to change.

Specifications

Dimensions (Approx.)	82.5 x 34 x 174.5mm (W x H x D) Except for the maximum protrusion
Weight (Approx.)	290g (Body only)
Operating temperature	0°C~+40°C
Storage temperature	-20°C~+60°C
Power consumption	0.2W below
Power-supply voltage	4.2~6.0 v ; supplied from Camcorders
Input/Output	CAMERA x3 / 2.5mm TRS Plug REMOTE x1 / 2.5mm TRS Jack OPTION x1 / 3.5mm TRS Jack

Gallery

