

## SNCA-POLE30

Mounting pipe for pendant mount applications



### Overview

Applicable Housing Models;

- SNCA-HRX550/EXT
- SNCA-HRX550/EXT/W
- SNCA-HRX550/INT
- SNCA-HRX550/EXT/R
- SNCA-HRX550/EXT/PRE
- SNCA-HRZ50/EXT
- SNCA-HRZ50/EXT/W
- SNCA-HRZ50/INT
- SNCA-HRZ50/EXT/R

Optional accessories;

- SNCA-CEILING (Ceiling Mount Adapter)

### Related products



#### **SNC- EB600**

Box-type 720p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



#### **SNC- EB600B**

Basic Box-type  
720p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



#### **SNC- EB630**

Box-type 1080p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



#### **SNC- EB630B**

Basic Box-type  
1080p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



## **SNC- VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- EP521**

Standard Definition  
(PAL) PTZ Network  
Camera



## **SNC- EP580**

1080p/30 fps PTZ  
Camera - E Series



## **SNC- ER521**

Standard Definition  
(PAL) Rapid Dome  
Network Camera



## **SNC- ER550**

720p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER580**

1080p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER585**

Outdoor Unitized  
1080p/30 fps Rapid  
Dome Camera - E  
Series

## Gallery

