

## UNI-MDPDH180

Pendant Mount Adaptor for outdoor Minidome Cameras



### Overview

The UNI-MDPDH180 is a 1-inch thread pendant adaptor for use with Sony SNC-VM632R/VM602R/EM632RC/EM602RC and SNC-DH160/DH180/DH260/DH280 video security cameras.

1" NPT pipe thread for pendant mounting. Also suitable for wall mounting (with UNI-WMB4 gooseneck wall mount bracket).

Kit includes gaskets and Teflon tape for water ingress protection outdoors.

All aluminium construction. Light grey finish. Suitable for outdoor or indoor use.

### Specifications

#### Architecture / Engineering Specifications

Size (H x W x D)	6.8 x 6.8 x 3.4 inches (173 x 173 x 86.4 mm)
------------------	--

Weight	0.9 lbs. (0.44 kg)
--------	--------------------

Body Construction	Aluminum
-------------------	----------

## Shipping

Weight	1.35 lbs. (0.6 kg)
--------	--------------------

Dimensions	9 x 8 x 4 inches ( 229 x 203 x 102 mm)
------------	--

## Mounting Accessories

UNI-CMA1	White aluminum corner mount
----------	-----------------------------

UNI-PMA1	White aluminum pole mount
----------	---------------------------

UNI-WMBB1	White aluminum wall / pole with (2) 23 inch mounting straps
-----------	---

UNI-WMB4	White aluminum wall mount
----------	---------------------------

## Compatible Camera Models

SNC-DH160 / SNC-DH180	720p HD, IR Vandal Resistant
-----------------------	------------------------------

SNC-DH260 / SNC-DH280	1080p HD, IR Vandal Resistant
-----------------------	-------------------------------

SNC-EM602RC / SNC-EM632RC	720p/30fps HD, IR Ruggedized E series 1080p/30fps Full HD, IR Ruggedized E series
---------------------------	---

SNC-VM602R / SNC-	720p/60fps HD, IR Ruggedized V
-------------------	--------------------------------

VM632R

series; 1080p/60fps Full HD, IR  
Ruggedized V series

---

## Related products



### **SNC- VM632R**

Outdoor IR  
Ruggedized 1080p/60  
fps Camera Powered  
by IPELA ENGINE EX™  
- V Series



### **SNC- VM602R**

Outdoor IR  
Ruggedized 720p/60  
fps Camera Powered  
by IPELA ENGINE EX™  
- V Series



### **SNC- EM630**

Minidome 1080p/30  
fps Camera Powered  
by IPELA ENGINE EX™  
- E Series



### **SNC- EM632RC**

Outdoor IR  
ruggedized 1080p/30  
fps camera powered  
by IPELA ENGINE EX™

## Gallery

