

## VPL-SW235

3,000 lumens WXGA Short Throw projector



### Overview

#### **Low Total Cost of Ownership(TCO) for widescreen, short throw, high brightness projector**

The VPL-SW235 short throw projector has a number of features to present high quality images while keeping low TCO. The projector also needs only 79cm to display a large 80-inch image on the screen, which fits perfectly in front of a white board leaving plenty of space. With the fuss-free installation and achievement of less glares or shadows during presentation, the short throw projector offers excellent usability.

#### **Short throw distance**

79cm for 80-inch image.

#### **3LCD Color Light Output colour reproduction and high brightness**

3000 lumen brightness with native WXGA (1280 x 800) 16:10 widescreen screen resolution.

#### **Long-lasting lamp**

10000 hours in Low mode.

#### **Wireless presentation with tablet (iOS or Android)**

The wireless presentation capability makes it easy to present files from your tablet device or smart phone.

## Features

### **Short throw distance**

The VPL-SW235 offers a 0.46:1 throw ratio that produces a 2.03m (80-inch) diagonal screen size image from only 79cm (31-inch) away from the screen.

### **High image quality 3LCD natural and vivid colour images**

Thanks to the optical system projecting three basic colours constantly each, the projector offers excellent light efficiency, which ensures colourful and bright images. High colour reproducibility is important especially when using colourful content, such as materials used in classrooms. The projector also has an excellent contrast ratio of 3000:1.

### **High brightness of 3000 lumen in High lamp mode**

The VPL-SW235 features three brightness modes for different use – 'High' for naturally white presentations in bright rooms, 'Standard' for everyday use, and 'Low' for video in darkened rooms. The native WXGA (1280 x 800) 16:10 widescreen screen resolution panel is perfect for presentations direct from a laptop or PC.

### **Energy efficient with long-lasting lamp of 10000 hours**

The lamp driver optimally controls the wattage of the lamp and achieves a long-lasting lamp time of 10000 hours with the brightness of lamp mode low. The recommended lamp replacement time is extended more than 66%, compared to the previous model.

### **Advanced energy-saving features**

Advanced lamp technology enables robust energy-saving features. For example, greater brightness control in Auto Light Dimming mode saves considerable energy when the projector is left on without being used. During projection, Auto Picture Mode automatically adjusts light output to suit the projected scene.

When you need to mute the picture temporarily, light output can be completely deactivated to minimise energy consumption.

## **Network presentation (LAN/Wireless LAN)**

When the projector is installed on a LAN/Wireless LAN, presentations can be projected from any PC and Mac on the network. A tablet or smart phone can be connected at the same time. The wireless presentation capability makes it easy to present files from your tablet device or smart phone. You can project jpg, pdf and other supporting formats. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. For Windows/Mac, an application "Projector Station for Network Presentation" is provided. For tablet/smartphone, an application is provided by Pixelworks, downloaded from the web. For details, please visit the following website: <http://PWPresenter.pixelworks.com>

## **Remote control for iOS device**

Projector Remote is simple remote control app for Sony's projectors. Networked projectors can be controlled by this remote app. Remote Control allows you to operate the projector with simple and easy-to-read buttons.

## **Networked control**

Projector functions and status can also be managed and monitored remotely from any user's PC on the network. For Windows, an application "Projector Station for Network Control" is provided.

## **USB Media viewer**

Insert a USB drive to effortlessly display photos, images and graphics with no PC needed.

## **USB display**

The projector allows you to display pictures and audio\* with one USB cable. You do not need to install any driver for this function. It is a convenient way to connect to the projector when you want

to connect easily.

\* There is a time lag in video and audio. When not in simple use, it is recommended to use Line-in or HDMI-in.

### **Built-in speaker**

The projector includes a 16W monaural speaker.

## Specifications

### Display system

Display system	3 LCD system
----------------	--------------

### Display device

Size of effective display area	0.59" (15 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--

Number of pixels	3,072,000 (1280 x 800 x 3) pixels
------------------	-----------------------------------

### Projection lens

Focus	Manual
-------	--------

Throw ratio	0.46:1
-------------	--------

### Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage	210 W type
---------	------------

## Recommended lamp replacement time\*1

Lamp mode: High      4000 H

---

Lamp mode: Standard    6000 H

---

Lamp mode: Low      10000 H

---

## Filter cleaning / replacement cycle (Max.)\*1

Filter cleaning /  
replacement cycle  
(Max.)      7000 H

---

## Screen size

Screen size      57" to 103" (1.45 m to 2.62 m)  
(measured diagonally)

---

## Light output

Lamp mode: High      3000 lm

---

Lamp mode: Standard    2100 lm

---

Lamp mode: Low      1700 lm

---

## Color light output

Lamp mode: High      3000 lm

---

Lamp mode: Standard 2100 lm

---

Lamp mode: Low 1700 lm

---

## Contrast ratio (full white / full black)\*2

Contrast ratio (full white / full black) 3000:1

---

## Speaker

Speaker 16 W x 1 (monaural)

---

## Displayable scanning frequency

Horizontal 14 kHz to 93 kHz

---

Vertical 47 Hz to 93 Hz

---

## Display resolution

Computer signal input Maximum display resolution: UXGA 1600 x 1200 dots\*3

---

Video signal input NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, The following items are available for digital signal (HDMI input) only;

1080/60p, 1080/50p

## Color system

Color system NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N

## Keystone correction (Max.)

Vertical +/- 7.5 degrees

## OSD language

OSD language 24-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)

## INPUT OUTPUT (Computer/Video/Control)

INPUT A RGB / Y PB PR input connector:  
Mini D-sub 15-pin (female)  
Audio input connector: Stereo mini jack

INPUT B	<p>RGB input connector: Mini D-sub 15-pin (female)</p> <p>Audio input connector: Stereo mini jack</p>
INPUT C	<p>HDMI input connector: HDMI 19-pin, HDCP support</p>
S VIDEO IN	<p>S video input connector: Mini DIN 4-pin</p> <p>Audio input connector: Pin jack (x2) (shared with VIDEO IN)</p>
VIDEO IN	<p>Video input connector: Pin jack</p> <p>Audio input connector: Pin jack (x2) (shared with S VIDEO IN)</p>
OUTPUT	<p>Monitor output connector*4: Mini D-sub 15-pin (female)</p> <p>Audio output connector*5: Stereo mini jack (variable out)</p>
REMOTE	<p>RS-232C connector: D-sub 9-pin (female)</p>
LAN	<p>RJ-45, 10BASE-T/100BASE-TX</p>
USB	<p>Type-A</p>
USB	<p>Type-B</p>
MICROPHONE IN	<p>Microphone input: Mini Jack</p>



---

## Acoustic noise

Lamp mode: Low      30 dB

---

## Operating temperature / Operating humidity

Operating temperature /  
Operating humidity      0°C to 40°C (32°F to 104°F) / 20% to 80% (no condensation)

---

## Storage temperature / Storage humidity

Storage temperature /  
Storage humidity      -10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)

---

## Power requirements

Power requirements      AC 100 V to 240 V, 3.2 A to 1.3 A, 50 Hz / 60 Hz

---

## Power consumption

AC 100 V to 120 V      Lamp mode: High: 315 W

---

AC 100 V to 120 V      Lamp mode: High: 302 W

---

## Power Consumption (Standby Mode)

---

AC 100 V to 120 V	0.5 W (when “Standby mode” is set to “Low”)
-------------------	---

AC 220 V to 240 V	0.5 W (when “Standby mode” is set to “Low”)
-------------------	---

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	5.0 W (LAN)
	5.6 W (optional WLAN module)
	5.8 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

AC 220 V to 240 V	5.3 W (LAN)
	5.9 W (optional WLAN module)
	6.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

## Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	After about 10 Minutes
---	------------------------

## Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch	1) Press the MENU button, then select [Connection/Power] 2) [WLAN Settings] 3) [WLAN Connection] 4) Select On or Off
--------------------------------------	--

## Heat dissipation

AC 100 V to 120 V	1075 BTU/h
AC 220 V to 240 V	1031 BTU/h

## Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Approx. 365 x 138.7 x 310 mm (14 3/8 x 5 15/32 x 12 7/32 inches)
---	---

## Mass

Mass	Approx. 4.4 kg (9 lb)
------	-----------------------

## Supplied accessories

Remote commander	RM-PJ8
------------------	--------

## Optional accessories

Replacement lamp	LMP-E212
------------------	----------

Wireless LAN Module	IFU-WLM3
---------------------	----------

## Notes

*1	This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used.
----	---

*2	The value is average.
----	-----------------------

*3	Available for VESA Reduced Blanking signal.
----	---

*4	From INPUT A and INPUT B.
----	---------------------------

*5	Works as an audio switcher function. Output from a selected channel; not available in standby.
----	--

Environmental notice for customers in the USA	Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see <a href="http://www.sony.com/mercury">www.sony.com/mercury</a> for
---	---

additional information.

---

## Gallery

