

ECM-674

Affordable shotgun Electret condenser microphone



Overview

The ECM-674 is an affordable shotgun-type electret condenser microphone, which delivers excellent sound performance in field and studio productions.

Superb Sound Quality

The ECM-674 offers an excellent sensitivity of -36 dB (0 dB=1 V/Pa.) and low inherent-noise level of less than 17 dB SPL. This allows the microphone to be used for clear voice pick-up even in noisy environments

Two-way Powering

A two-way powering capability allows the ECM-674 to be driven by microphone power or batteries, making it suitable for both camcorder mounting and many other sound-gathering applications. Internal: AA-size battery operation. External: DC (40 to 52 V) operation

Built-in Battery Liquid Leakage Protection Circuit

In general, old batteries can leak and damage the equipment they are used in. The ECM-674 prevents this by continually detecting the output voltage of the battery and shutting off the power supplied to the electric circuit whenever the voltage drops beneath a certain threshold.

Features

Flat-and-wide Frequency Response

The ECM-674 microphone has a flat-and-wide frequency response (40 Hz to 20 kHz) and provides sound reproduction that is extremely smooth and natural

Compact and Lightweight Design

The ECM-674 has been designed as a highly directional compact and lightweight shotgun microphone. It measures only 268 mm (10 5/8 inches) in length and weighs just 185 g (6.5 oz), maintaining good balance even when mounted on compact camcorders.

Built-in Low Cut Filter

The built-in two-position (M, V) low-cut switch provides users with a simple method of reducing the effects of undesired ambient noise.

Specifications

Audio Section

Capsule Type	Mono Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Uni-directional (super-cardioid)
Sensitivity *[1]	-36 dB ±3 dB

Audio Section

Output Impedance *[2]	220Ω±20%, Balanced
Dynamic Range	Phantom: 107 dB or more Battery: 98 dB or more
Signal-to-Noise Ratio *[3]	77 dB or more
Inherent Noise *[4]	17 dB SPL or less
Induction Noise From External Magnetic Field *[5]	0 dB SPL or less
Wind Noise *[6]	50 dB SPL (without windscreen) 45 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level *[7]	Phantom: 124 dB SPL Battery: 115 dB SPL

General Section

Connector	XLR-3-12C (male)
Mic Cable	XLR-3 to XLR-3 500 mm 19.6 inches
Power Requirements	External: DC 40 V to 52 V Battery: 1.5 V
Dimensions *[8]	φ20 x 268 mm φ13/16 x 10 5/8 inches
Mass	Approx. 7.3 oz with battery Approx. 6.5 oz without battery Approx. 208 g with battery Approx. 185 g without battery
Supplied Accessories	Windscreen (1) Stand adaptor (2) Short XLR cable Operating instructions (1) Mic spacer (2) Mic holder (1)

Notes

Note	*[1] 0 dB = 1 V/Pa, at 1 kHz *[2] Output impedance at 1 kHz *[3] A-weighted, 1 kHz, 1 Pa. *[4] 0 dB SPL = 20 μPa. *[5] dB SPL/1E-7 T, 0 dB SPL = 20 μPa. *[6] Wind noise at 2m/s (0 dB SPL = 20 μPa.) *[7] 0 dB SPL = 20 μPa. *[8] The values for dimensions are approximate.
------	--

Related products



HXC-FB80

Three 2/3-inch Exmor™
CMOS sensor HD colour
studio camera

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.