

1/3-inch CMOS sensor SD /  
HD robotic camera



Overview

**Excellent Picture Quality**

**Flexible Installation - Ceiling Mount or Flat Surface**

**Easy-to-use and Ergonomically Designed Remote Control Unit**

**High Performance Pan/Tilt/Zoom Mechanism**

**Compact Size and Silent Mechanism**

**18x Optical Zoom (72x With Digital Zoom)**

**1080i, 720p, and SD Output**









## Related products



### **BRBK-SF1**

HD optical multiplex card for BRC-H900P and BRC-Z330 robotic cameras



## Gallery



