

MSU-1500

Master setup unit, multi camera remote control panel for HDC / HSC cameras (vertical type)



Overview

The MSU-1500 master setup unit is a control panel for camera configuration and maintenance. It is a compact, vertically-oriented device (as opposed to the MSU-1500, which has a larger, horizontally oriented panel), and can control multiple camera systems, using either the CNU-700 Camera Command Network Unit, or using a LAN, in which case up to 96 cameras can be controlled.

This product contains pre-installed software and requires the purchase of licence keys to activate some functions.

Features

Large and flexible system configuration

The MSU-1500 is part of a family of products that provides flexibility in the configuration of large and small camera control systems.

Ethernet LAN capability

The MSU-1500 supports inter-connectivity using an Ethernet LAN as well as a CNU-700.

Customisable Switch and menu

MSU-1500 users can map any function to an assignable switch or menu item

Specifications

General

| | |
|--|---|
| Power supply | AC 100 - 240 V. 50/60 Hz 0.35 A (Max.) DC 10.5 - 17 V 1.2 A (Max.) |
| Operating temperature | 5 °C to 40 °C (41 °F to 104 °F) |
| Dimensions (W x H x D) (excluding protrusions) | 204 × 354 × 67 mm (8 1/8 × 14 × 2 3/4 in.) |
| Mass | Approx. 3.6 kg (7 lb. 15 oz.) |

Input/output connectors

| | |
|----------|------------------------------------|
| Ethernet | RJ-45 8-pin (X1) |
| CCU/CNU | Multi-connector 8-pin, female (x1) |
| AUX | Multi-connector 8-pin, female (x1) |
| EXT I/O | D-sub 50-pin, female (x1) |
| AC IN | 3-pin (x1) |
| DC IN | 4-pin (x1) |

Related products



HDC-P43

4K/HD POV Camera



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



HDC-3170

Three 2/3-inch CMOS sensors portable system camera for triax operation



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



HDC-P31

HD compact POV system camera with enhanced remote features and advanced HDR workflows



RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)

Gallery

