

## XVS-2M/E Pack

3G-capable, 4K-ready, IP-ready XVS Series Switchers in an affordable pack



### Overview

#### The Essence of a High-End XVS Series Switcher in a Pack

The XVS-2M/E Pack is brimming with Sony's powerful feature set, long-established and ever-evolving in its MVS and XVS Series switchers. These convenient, affordable packs can also be used to produce 1080p (3G).

#### 20-Channel Frame Memory and Clip Transition

The XVS Pack supports 20 channels of frame memory. Using this memory feature, you can create clip transition effects – transitioning a CG image (such as a logo) and moves across the picture from one side to the other with audio, while a background transition is performed in the background.

#### Powerful Key Resizer (2.5D DME)

A powerful resizer function is provided for every keyer. 8 x 2.5D DME effects can be utilized in the system, which is very useful for optimizing on-screen composition. For example, you can create multiple picture boxes within a single screen.

#### Input Format Converter and Frame Synchronizer

Format converter (FC) and frame synchronizer (FS) functions are provided for every input as standard. You can input various types of signal to the system, including different video formats or even non-locked signals. The following incoming signal formats are supported in FC: 480i, 576i, 720p, 1080i, and 1080p Level-B.

#### 2-Channel Multi-Viewer

Each XVS Pack has two standard multi-viewer channels, enabling up to a 32-screen monitoring environment without any additional external multi-viewer systems.

#### Future Proofing Production Switcher (Option)

The XVS Pack also supports 4K (UHD) with purchase of an optional software and a video-over-IP interface with optional hardware.

### Features

#### XVS-2M/E Pack

- 2M/E 20XPT Compact Panel
- 4 Keyers per M/E
- 32 Inputs, each has Format Converter and Frame Synchronizer
- 24 Outputs
- 20ch Frame Memory
- 2ch Multi Viewer
- Tally, GPIO, Device Control

#### Source Name and Color Indicator (LED)

Source Name, Bus Name, or attached Macro Name can be displayed. Source color can be changed by RGB parameters.

#### Utility and ShotBox

24-color LCD buttons with 17 assignable buttons. Utility/ShotBox recall, Keyframe/Macro editing, and Transition rate change.

## Related products



NETWORKED **LIVE**




### **XVS-6000**

Entry-level 4K/3G/HD video switcher for IP and SDI

### **ICP-X7000**

Control panel for MLS-X1 and XVS series switchers

## Gallery



---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.