

## UNI-ID7T3

Tinted glass recessed camera housing



### Overview

#### **Tinted Recessed Indoor Ceiling Housing for dome security cameras**

The 7-inch diameter Recessed Indoor Ceiling mount type Housing is used for SNC-RX series, SNC-RZ25N, RZ30N and RZ50N cameras. It has a tinted dome and white trim ring. No electronics. Interface wiring (Ethernet, sensor, I/O, power provided by user).

#### **Anti glare**

7-inch diameter Tinted polycarbonate lower dome.

### Features

#### **Discrete**

White trim ring.

#### **Ceiling mounting**

Plenum Rated metal top.

## Gallery

