

## BRC-H900

Full HD robotic studio camera with 1/2-type Exmor 3CMOS sensor and 14x optical zoom



### Overview

#### **Remotely capture broadcast quality Full HD images with smooth, silent PTZ**

The BRC-H900 remote studio camera combines uncompromising broadcast picture quality with the flexibility of PTZ operation.

Designed for unattended operation, this compact but powerful robotic camera is an ideal complement to other broadcast cameras for capturing images in hard-to-reach or unobtrusive positions. It's equally at home in TV newsrooms, remote studios and on-air suites, auditoriums, houses of worship, courtrooms or outdoor sports events.

The sensitive 1/2-type Exmor 3CMOS image sensor captures detail-packed Full HD footage with low noise and a wide dynamic range. Smooth, speedy remote PTZ with 14x optical zoom and on-board image stabilisation accommodates wide-angle scenes and tightly framed close-ups. Broadcast-friendly features include dual tally lamps for on-air operation, while operational flexibility is enhanced with options for ceiling, table top or tripod mounting.

There's also a broad range of video interface and remote control possibilities, simplifying smooth integration into any broadcast or professional AV environment.

### Features

#### **Broadcast quality Full HD images**

The BRC-H900 delivers uncompromised broadcast quality colour pictures in Full HD, thanks to three 1/2-inch type Exmor CMOS sensors. Advanced picture adjust functions include matrix, colour correction, white, detail, knee, gamma, master black, black gamma and flicker cancel.

#### **High quality 14x optical zoom lens**

The high quality lens with 14x optical zoom range covers wide angle shots as well as tight close-ups, making the BRC-H900 ideal for use in a wide range of applications, from broadcast studios to conference halls, boardrooms and outdoor events.

#### **Excellent low light sensitivity**

With high sensitivity (F10) and excellent minimum illumination (4 lx), the BRC-H900 can capture crisp, low noise pictures even in dimly lit studios and meeting rooms.

#### **Smooth, silent Pan/Tilt/Zoom (PTZ) operation**

Accurately re-frame shots or track moving subjects with smooth, speedy remote control of pan, tilt and zoom functions. There's also a slow pan/tilt mode for precise, judder-free low-speed camera movements. Near-silent operation makes the camera

ideal for broadcast studios and other noise-conscious environments.

**Steadier, more stable images**

On-board image stabilisation ensures crisper, more stable images in situations where the camera is subject to movement and vibration.

**Flexible installation**

The BRC-H900 is equally suitable for ceiling, desktop or tripod mounting, with an 'Image Flip' function that automatically ensures the correct output orientation in any installation environment. Ceiling bracket included.

**Remote operation**

Pan/tilt/zoom and other camera settings can be controlled using the supplied IR remote commander, or with the optional RM-BR300 Remote Control Unit that can control multiple cameras.

**Optional IP control**

Large-scale systems of up to 112 BRC-H900 cameras can be controlled over standard IP networks by adding the optional BRBK-IP10 IP remote control board and RM-IP10 remote controller.

**Versatile video outputs**

Extensive video outputs - including HD/SD-SDI, component and composite Y/C - give greater installation flexibility in professional broadcast and AV environments.

**Wide range of expansion options**

The camera can be configured with a choice of optional accessory cards, including the BRBK-HSD2 (HD/SD-SDI output), BRBK-SA1 (Analogue SD output), BRBK-SF1 (HD optical multiplex) and BRBK-IP10 (IP control). Also available are the BRU-SF10HD optical multiplex unit and CCFC-S200 optical fibre cable for operation over long distances.

**Front and rear tally lamps**

Ideal for on-air broadcast use, the BRC-H900 features dual tally lamps on the front and rear of the camera body. Brightness of the front tally lamp can be adjusted in two steps.

Specifications

Camera	
Image Sensor	1/2-type Exmor CMOS x3
Image Sensor (Number of Effective Pixels)	2.07 Megapixels x3
Image Sensor (Total Number of Pixels)	Approx. 3.01 Megapixels
Signal System	60 Hz: 1080/59.94i, 720/59.94P, NTSC 50 Hz: 1080/50i, 720/50P, PAL
Sensitivity	F10
Minimum Illumination (50IRE)	4 lx (50IRE, F1.9, +24 dB)
Horizontal Resolution	>1,000 TV line (in HD-SDI output)
S/N Ratio	50 dB

Gain	Auto/Manual (-3 dB to +24 dB)
Shutter Speed	1/8,000 s to 1/60 s or 1/8,000 s to 1/50 s
Exposure Control	Auto, Manual, Priority mode (shutter priority & iris priority), Back light, Spot light
Color AE Function	No
White Balance	Auto/Indoor/Outdoor/One-push/Manual
Optical Zoom	14x
Digital Zoom	-
Focusing System	Auto/Manual
Horizontal Viewing Angle	59.6° (Wide-end)
Focal Length	f=5.8 mm to 81.2 mm F1.9 (Wide), F2.8 (Tele)
Minimum Object Distance	300 mm (Wide), 800 mm (Tele)
Pan/Tilt Angle	Pan: ±170° Tilt: +90°/-30°
Pan/Tilt Speed	Pan: 0.22° to 60°/s Tilt: 0.22° to 60°/s
Preset Position	16

### Camera Features

Auto ICR	No
Wide-D	No
Image Stabilization	Yes
Image Flip	On/Off
ND Filter	No
Color Gain	No
Color Hue	No
Color Matrix	ON/OFF
Color Detail	ON/OFF
Skintone Detail	No
Gamma	STD1/STD2/STD3/STD4/CINE1/CINE2/CINE3/CINE4
Gamma Level	-99 to 0 to +99
Black	-99 to 0 to +99
Black Gamma	-99 to 0 to +99
Knee Point	50 to 90 to 109

Knee Slope	-99 to 0 to +99
Knee Sat Level	0 to 50 to 99
Auto Focus Assist Function	No
Flicker Cancel	On/Off
B&W	No
Color Bar	On/Off

## Interface

HD Video Output	HD/SD-SDI(switchable) Component (Y/Pb/Pr) or RGB, HD, VD or SYNC
SD Video Output	Composite, Y/C
Camera Control Interface	RS-232C/RS-422 (VISCA)
External Sync. Input	Yes

## General

Power Requirements	DC 10.8 V to 13.2 V
Power Consumption	Max 28.8 W (without optional cards)
Operating Temperature	0 °C to 40 °C 32 °F to 104 °F
Storage Temperature	-20 °C to +60 °C -4 °F to +140 °F
Dimensions (W x H x D) *1	198 x 260 x 238mm 7 7/8 x 10 1/4 x 9 3/8 inch
Mass	5.0 kg 11 lb 0.37 oz
Optional Card Slot s	Yes
Body Color	Silver
Size of Screw Hole for Tripod	Φ5 depth 5
Mountable Angle	< ±15°
Ceiling Mount	Yes
Supplied Accessories	IR Remote Commander Unit (1) AC power adaptor (1) AC power cord (1) RS-422 connector plug (1) Ceiling bracket (2)

- Wire rope (1)
- Screws(M3 x 8) (7)
- Screws(M4 x 8) (1)
- Operating instructions (1)

\*1

The values for dimensions are approximate.

Accessories



**BRU-SF10**  
HD/SD Optical Multiplex Unit for BRC-H900 and BRC-Z330 cameras



**AWS-750**  
Anycast Touch portable live content producer



**RCP-1500**  
Joystick type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



**HZC-BRCN1**  
Software for CNA-1 to control paint parameters of BRC-H900 from PCP-1500/1530



**BRBK-SF1**  
HD optical multiplex card for BRC-H900P and BRC-Z330 robotic cameras



**RM-IP10**  
IP remote control panel for BRC cameras



**RM-IP500**  
PTZ Camera Remote Controller



**RCP-1530**  
Joystick type of Remote control panel for HDC/HSC/HXC series cameras. 5 units in 19-inch EIA rack.



**NXL-IP55**  
IP Live Production Unit



**CNA-1**  
Camera control network adaptor

## Gallery

