

30-inch 4K TRIMASTER EL™ OLED critical reference monitor



4K

SR Live
for HDR

HDR

Overview

4K OLED unleashed

Full 4K picture resolution

High Dynamic Range

Supports DCI P3 and ITU-R BT.2020 wide colour spaces

Multi-format capability

Safe area and aspect markers

Input Setting

Shopping channels

Gamut Marker

Relative contrast 1/2, 1/3 and 1/4

Features

High Dynamic Range mode

Supports DCI P3 and ITU-R BT.2020 wide colour spaces

**HDMI (HDCP2.2) and 3G-SDI Quad-link up to 4096 x 2160/48p 50p 60p,
YCbCr 4:2:2 10-bit**

Accurate black and colour reproduction

Quick Response with Virtually No Motion Blur

Extremely wide viewing angle

Sony S-Log Gamma, SMPTE ST 2084 and HLG Support

Flicker free mode


Interlace mode

Safe area and aspect markers

Flexible area markers*

Time code function*

Specifications



Related products



PVM-X550
55-inch 4K TRIMASTER EL™ OLED high grade picture monitor



PXW-FS7M2
4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



PMW-PZ1
4K/HD SxS memory player



BVM-E171
16.5-inch TRIMASTER EL™ OLED critical reference monitor with wide viewing angle supports 4K production



PMW-F55
Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output



F65
Super 35mm 8K CMOS sensor SRMASTER camera



HDC-4300
4K/HD System Camera



HXC-FB80
Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



MVS-8000X
4K, HD, 3G, SD Multi-Format Production Switcher Processor



HDRC-4000
HDR Production Converter Unit



PMW-F5
Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K on SxS memory plus 16-bit RAW 2K/4K output



PXW-FS7
4K Super 35mm Exmor CMOS sensor XDCAM camera with α Mount lens system, 4K/2K RAW and XAVC recording options



HDC-P43

4K/HD POV Camera



BVM-E251

24.5-inch TRIMASTER EL™
OLED critical reference
monitor with wide viewing
angle supports 4K production

Gallery

