

DWT-B03R



Superb audio quality and stable operation in a wide range of environments

The third generation of Sony's acclaimed DWX series, this high performance digital wireless bodypack transmitter is an ideal choice for live sound applications including theatre and concerts, as well as studio based TV production and ENG/EFP.

Light and compact (27% smaller than its DWT-B01N predecessor), the DWT-B03R features a tough magnesium body that's resistant to rain, spray and sweat.

Sony's advanced digital audio processing, encryption and RF transmission technologies assure secure, stable transmission and reception of very high quality audio with low latency.

The DWT-B03R is ideal for use in large-scale multi-channel productions, supporting up to 21 simultaneous channels per 8MHz TV band or up to 16 simultaneous channels per 6MHz TV band.

The DWT-B03R is compatible with Sony Wireless Studio control software for PC (Ver 5.0 or later), allowing flexible remote operation. Remote control of up to 82 transmitters is possible using the Cross Remote™ function combined with the RMU-01 remote control unit (available separately).

Small, lightweight and robust magnesium body

27% smaller than its DWT-B01N predecessor

Very high quality wireless audio

Advanced Sony codec design assures superb audio quality, with a high dynamic range of more than 106 dB, plus a wide frequency response of 20 Hz - 22 kHz and excellent transient response.

Low-latency audio

Advanced Sony codec design reduces audio latency to as little as 1.2msec*

*DWT-B03R and DWR-R03D total delay with codec mode2 and analog output

Rain, sweat and spray proof*

Ideal for musical, film production or outdoor operation, the DWT-B03R features a tough magnesium body with a moisture-resistant housing gasket and splash-proof connector that resists rain, sweat and spray.

*IPX4/IPX5 rating based on standard testing by Sony.

Long battery life

Perform for longer with the high-capacity rechargeable NP-BX1 Li-ion battery (approx. 7 hours). The DWT-B03R is compatible with the optional BC-DWX1 Dual Charger.

148MHz* wideband

Contributes to the reduction of equipment and burden of maintenance.

*depends on version

High density multi-channel operation

Ideal for large-scale productions, the DWT-B03R supports high-density simultaneous multi-channel operation: 375kHz spacing accommodates up to 21 channels per 8MHz TV band or up to 16 simultaneous channels per 6MHz TV band.

AES 256bit encryption

For secure encrypted transmission

Easy, versatile remote control

The DWT-B03R is compatible with Sony's Wireless Studio control software for PC (Version 5.0 or later). Up to 82 transmitters can be controlled using the Cross Remote™ function and RMU-01 remote control unit (available separately).

Selectable RF output power

RF output power level is selectable (2mW/10mW/25mW) to prioritise stable multi-channel or long distance operation.

OLED display

The easy-to-read OLED display gives confirmation of channel number, RF signal status, user name, user group and lock status.

Phase reverse mode

It can change the audio phase by the menu.

User setting memory

Settings can be easily stored to the memory of DWT-B03R.

Setting lock

Transmitter settings can be locked to prevent accidental operation during performance.

Transmitter/receiver identifying function

Paired transmitters/receivers are identified by blinking display.

Small 3-pin connector with lock

Specifications

Wireless Interface	WiDIF-HP
Oscillator Type	Crystal-controlled PLL Synthesizer
Antenna Type	λ/4 flexible wire
Type of Emission	G1E or G1D
Carrier Frequencies - UC7	470.125 MHz to 607.875 MHz, 614.125 MHz to 615.875 MHz, 25 kHz steps

Carrier Frequencies - CE7	L: 470.025 MHz to 614.000 MHz, 25 kHz steps H: 566.025 MHz to 714.000 MHz, 25 kHz steps
Carrier Frequencies - J	L: 470.150 MHz to 614.000 MHz, 25 kHz steps MH: 566.025 MHz to 713.850 MHz, 25 kHz steps G: 1240.150 MHz to 1251.825 MHz, 1253.175 MHz to 1259.850 MHz, 25 kHz steps B: 806.125 MHz to 809.750 MHz, 125 kHz steps
RF Power	2 mW/10 mW/25 mW (e.r.p) selectable
Input Connector	Small 3-pin connector with lock
Reference Input Level	MIC: -60 dBV (-58 dBu), 1 kHz (at 0-dB attenuator level) / LINE: +4 dBu, 1 kHz
Maximum Input Level	MIC: -22 dBu (with 0 dB attenuator), LINE: +24 dBu
Audio Attenuator Adjustment Range	0 to 48 dB (3 dB steps, MIC input mode only)
Frequency Response	Transmission: 20Hz to 22kHz (typical)
Dynamic Range	106 dB typical (A-weighted, T.H.D=1%)
Distortion (T.H.D)	MODE1, MODE2: 0.03% or less, MODE3: 0.3% or less
Audio Delay*	MODE1: 0.8 msec (total: 2.7msec) /MODE2: 0.7 msec (total: 1.2msec)/MODE3: 1.8 msec (total 3.7msec) *Analog output
Wireless Remote Control	Cross Remote (2.4- GHz IEEE802.15.4 compliant)
Display	OLED
Power Requirements	DC 3.6 V (with Rechargeable Battery Pack: NP-BX1)
Battery Operating Time	Approx. 7 hours with Sony's NP-BX1 at 25°C(77°F) at 10-mW output (with the wireless remote control function off and DIMMER MODE set to AUTO OFF)
Operating Temperature	0°C to 50°C / 32°F to 122°F
Storage/Transport Temperature	-20°C to +60°C / -4°F to +140°F
Dimensions (W x H x D)	Approx. 53 x 60 x 17 mm (60 x 60 x 17 mm with the projection parts) (excluding the antennas)
Mass	Approx. 99 g

Supplied Accessories

- Belt Clip (1)
 - Carrying case (1)
 - NP-BX1 (1)
 - Scribble sheet (1)
 - CD-ROM (1)
-



