

# ECM-673

Short Shotgun Electret Condenser Microphone.



## Overview

The ECM-673 is a short shotgun, electret condenser-type microphone, which delivers excellent sound performance in field and studio production applications at an affordable price.

## Features

### Superb Sound Quality

The ECM-673 offers an excellent sensitivity of -36 dB (0 dB=1 V/Pa) and a low inherent-noise level of less than 17 dB SPL. This allows the microphone to be used for clear voice pickup, even in noisy working environments.

### Flat-and-wide Frequency Response

The ECM-673 microphone has a flat-and-wide frequency response (40 Hz to 20 kHz) and delivers extremely smooth and natural sound reproduction.

### Compact and Lightweight Design

The ECM-673 has been designed as a highly directional, compact, and lightweight short shotgun microphone. It measures only 200 mm (7 7/8 inches) in length, and weighs just 135 g (4.76 oz), maintaining good balance even when mounted on compact camcorders.

### High Durability and Reliability

The vibration-resistant mechanism of the ECM-673 offers high durability and reliability, making it suitable for the harsh environments that can be encountered in field sound-acquisition.

### Built-in Low-cut Filter

The built-in two-position (M, V) low-cut switch on the ECM-673 provides a simple method of reducing the effects of unwanted ambient noise.

## Specifications

Audio Section	
Capsule Type	Mono Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Uni-directional (super-cardioid)
Sensitivity *[1]	-36 dB ±3 dB
Output Impedance *[2]	220Ω±20%, Balanced

Dynamic Range	107 dB or more
Signal-to-Noise Ratio *[3]	77 dB or more
Inherent Noise *[4]	17 dB SPL or less
Induction Noise From External Magnetic Field *[5]	0 dB SPL or less
Wind Noise *[6]	50 dB SPL (without windscreen) 45 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level *[7]	124 dB SPL

**General Section**

Connector	XLR-3-12C (male)
Mic Cable	XLR-3 to XLR-3 500 mm 19.6 inches
Power Requirements	External, DC 40 V to 52 V
Dimensions *[8]	φ20 x 200 mm φ13/16 x 7 7/8 inches
Mass	Approx. 4.8 oz Approx. 135 g
Supplied Accessories	Windscreen (1) Stand adaptor (2) Short LR cable (for camcorder use) (1) Operating instructions (1) Mic spacer (2) Mic holder (1)

**Notes**

Note	<p>*[1] 0 dB = 1 V/Pa, at 1 kHz                  *[2] Output impedance at 1 kHz                  *[3] A-weighted, 1 kHz, 1 Pa.                  *[4] 0dB SPL = 20? Pa.                  *[5] dB SPL/1E-7 T, 0 dB SPL = 20? Pa.                  *[6] Wind noise at 2m/s (0 dB SPL = 20?Pa.)                  *[8] The values for dimensions are approximate.</p>
------	--

Related products



**HXC-FB80**

Three 2/3-inch Exmor™ CMOS



## Gallery

