

ECM-678

Shotgun Electret condenser microphone



Overview

For superior sound quality, choose the ECM-678. It delivers superior sensitivity of -28 dB (0dB=1V/Pa) and extremely low inherent noise of less than 16 dB SPL. This microphone balances the need for a compact size with its ability to deliver excellent performance. The result is a highly directional microphone that is only 250 mm in length.

Specifications

Audio Section	
Capsule Type	Mono Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Uni-directional (super-cardioid)
Sensitivity *[1]	-28 dB +/-3dB
Output Impedance *[2]	200Ω±20%, Balanced
Dynamic Range	111 dB or more
Signal-to-Noise Ratio *[3]	78 dB or more
Inherent Noise *[4]	16 dB SPL or less
Induction Noise From External Magnetic Field *[5]	0 dB SPL or less
Wind Noise *[6]	60 dB SPL or less (without screen)
Maximum Input Sound Pressure Level *[7]	127 dB SPL
General Section	
Connector	XLR-3-12C (male)
Mic Cable	XLR-3 to XLR-3 480 mm 18.9 inches
Power Requirements	External, DC 48 V +/-4 V

Dimensions *[8]	φ20 x 250 mm φ13/16 x 9 7/8 inches
Mass	Approx. 7 oz Approx. 200 g
Supplied Accessories	Windscreen (1) Stand adaptor (2) Short LR cable (for camcorder use) (1) Operating instructions (1) Mic spacer (2) Mic holder (1) Carrying case (1)

Notes

Note	<p>*[1] 0 dB = 1 V/Pa, at 1 kHz *[2] Output impedance at 1 kHz *[3] A-weighted, 1 kHz, 1 Pa. *[4] 0dB SPL = 20? Pa. *[5] dB SPL/1E-7 T, 0 dB SPL = 20? Pa. *[6] Wind noise at 2m/s (0 dB SPL = 20?Pa.) *[7] 0 dB SPL = 20? Pa. *[8] The values for dimensions are approximate.</p>
------	---

Related products



HXC-FB80
 Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera

Gallery

