

ECM-90LM

Electret condenser microphone



Overview

Ultra-miniature, omni-directional electret condenser lavalier microphone designed for quality-critical applications in ENG, Studio, EFP, and Location Sound applications. Dual diaphragm design contributes to high sensitivity, wide dynamic range, and low noise. Generous diaphragm mounting architecture radically reduces common cable noise associated with lavalier microphone designs. Flat and wide frequency response (20Hz – 20kHz) provides natural sound reproduction. Water resistant design maintains sound clarity in almost any application or environment. Shielded for use with digital wireless transmitters.

Specifications

Audio Section

Capsule Type	Electret Condenser
Frequency Response	20 Hz to 20 kHz
Directivity	Omni-directional
Sensitivity *[1]	-40 dB (10mV)
Output Impedance * [2]	6.3 kΩ (unbalanced)

Dynamic Range (typ.)	99 dB
Signal-to-Noise Ratio (typ.) *[3]	68 dB
Inherent Noise (typ.) *[4]	26 dB SPL
Wind Noise *[5]	45 dB SPL or less (with supplied windscreen)
Maximum Input Sound Pressure Level (typ.) *[6]	125 dB SPL

General Section

Connector	3-pin Lemo connector
Mic Cable	5.2 feet 1.6m
Power Requirements	Supplied from Sony wireless system transmitters
Dimensions *[7]	5/32 x 5/32 x 21/26 inches (Mic head) 3.5 x 3.5 x 20.5 mm (Mic head)
Mass (microphone body, excluding cable)	Approx. 0.035oz Approx. 1g

Supplied Accessories	Urethane type windscreen (1) Single/vertical type tie clip (1) Single/horizontal type tie clip (1) Operating instructions (1)
Optional Accessories	Wind screen pack Vertical clip pack Safety clip pack Horizontal clip pack Double clip pack Color windscreen pack Black windscreen pack Accessory kit

Notes	
*[1]	0 dB = 1 V/Pa, at 1 kHz
*[2]	Output impedance at 1 kHz
*[3]	A-weighted, 1 kHz, 1 Pa
*[4]	0dB SPL = 20 μPa
*[5]	Wind noise at 2m/s (0 dB SPL = 20 μPa)
*[6]	0dB SPL = 20 μPa
*[7]	The values for dimensions are approximate.

Related
products



DWT-B03R

DWX Series digital
wireless microphone
bodypack transmitter

Gallery

