

## HDVF-L10

### 3.5" Colour LCD HD Viewfinder



#### Overview

3.5" Colour LCD HD Viewfinder for cameras with a round-type 20-pin viewfinder interface. The applicable cameras output the higher resolution QHD signal to this viewfinder. Camera operators can see the LCD, directly, because the optical loupe and the elbow parts can be flipped-up.

#### **3.5" Colour LCD QHD Viewfinder**

#### **Uses round-type 20-pin viewfinder interface**

#### **Switchable display mode**

#### Specifications

##### General

Power supply	10.5 to 17.0 V DC (supplied by the camera)
--------------	--------------------------------------------

Power consumption	3.3 W
-------------------	-------

Operating temperature	-5°C - 45°C
-----------------------	-------------

Storage temperature	-20C to +60C (-4 F to +140 F)
---------------------	-------------------------------

Mass	700 g
External dimensions	201mm (8 in) x 255mm (10 1/8 in) x 60mm (2 3/8 in) 89mm (3 5/8 in)
3.5-inch colour TFT transfective LCD Image display area dimensions	76.8 × 43.2 mm (3 1/8 × 1 3/4 inches) (H/V, 16:9 aspect ratio)

## Performance

Brightness	200 cd/m <sup>2</sup> (typical) (when eyepiece is attached)
Resolution	500 lines or more
Colour temperature	6500 K (typical)

## Connector

Connector	Round-type 20-pin connector
-----------	-----------------------------

## Supplied accessories

Supplied accessories	Operation manual (1)
----------------------	----------------------

## Optional accessories

Viewfinder Rotation Assembly :

Optional accessories    BKW-401

---

## Compatible products

Compatible products    HXC-FB75KC, HXC-FB75H, HDC-1700, HDC-2400, HDC-2500, HDC-2570, HDC-3300R, HDC-4300, HSC-100R, HSC-100RF, HSC-300R, HSC-300RF, PDW-680, PDW-700, PDW-850, PDW-F800, PMW-500, PXW-X400, PXW-X500

---

## Notes

Notes    Design and specifications are subject to change without notice.

---

## Related products



### **HXC-FB80**

Three 2/3-inch  
Exmor™ CMOS sensor  
HD colour studio  
camera

## Gallery

