

## LA-FZB2

Lens mount adaptor from B4  
mount to FZ mount



### Overview

#### **Enables the use of existing HD lenses for 4K production with PMW-F55**

The LA-FZB2 lens mount adaptor increases the lens options for the PMW-F55 camcorder shooting 4K productions. The small and lightweight lens mount adaptor converts the lens mount format from B4 to FZ. It enables the use existing HD lens including HD BOX lens for Sports shooting, while maintaining good operational weight balance.

#### **Integrates motorised ND and CC filters**

With the LA-FZB2, you are able to change ND and CC filters remotely. The system incorporates the same RCP/MSU operation system as current HDC Series cameras.

### Features

#### **Mount lens adaptor from B4 to FZ mount for 4K/HD shooting**

The LA-FZB2, operating with the PMW-F55 camcorder, allows you to convert the lens mount format from B4 to FZ including 12pin B4 lens connector. It enables you to use existing HD lens, including HD BOX lens for sports shooting.

#### **Motorised ND and CC filter disks integrated**

The LA-FZB2 gives you the same RCP/MSU operation as current HSC Series system cameras. With the motorised ND and CC filters

fully integrated, you are able to change the filters remotely.

### **Small and lightweight**

The LA-FZB2 has small proportions (W91mm x H173.4mm x D96mm) and weighs only 1Kg, making it easy-to-handle and allowing you to maintain a good operational weight balance with the PMW-F55.

Related  
products



### **PWS-4400**

4K / HD multi-port AV  
storage unit

## Gallery

