

RM-30BP

Remote Commander



Overview

The RM-30BP is the successor to the RM-1000BP, the industry's first comprehensive, multifunctional remote commander.


Ideal for freelancers and small-budget productions, the lightweight remote can be handheld, placed on a table or attached to a tripod arm for operation. The RM-30BP can control most camera functions including:

- Lens control: one push auto / manual focus, iris and zoom control
- Camera control: recording / display functions, shutter speed, white balance - including six assignable buttons
- Playback and multi camera control (up to 3 cameras)

The RM-30BP is compatible with a wide-range of Sony camcorders, including PXW-FX9 and ILME-FX6. Please consult Resources section for latest Compatibility Notes PDF.

Specifications

Notes	
Specifications are tentative and subject to change.	
Specifications	
Dimensions (Approx.)	82.5 x 34 x 174.5mm (W x H x D) Except for the maximum protrusion
Weight (Approx.)	290g (Body only)
Operating temperature	0°C~+40°C
Storage temperature	-20°C~+60°C
Power consumption	0.2W below
Power-supply voltage	4.2~6.0 v ; supplied from Camcorders
Input/Output	CAMERA x3 / 2.5mm TRS Plug REMOTE x1 / 2.5mm TRS Jack OPTION x1 / 3.5mm TRS Jack



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 20 2026