

AC-VQ1051D

L series battery AC adapter/charger



Overview

Power supply / charger compatible with InfoLITHIUM L series batteries

- Charging time (normal charge / full charge): F570 110 min. / 170 min. ; F770 185 min. / 245 min. ; F970 285 min. / 345 min.
- Information display shows remaining amount and current battery levels in percentage.
- Relay connections for charging up to two batteries at the same time.
- Includes car charging cord DCC-VQ1

Specifications

Basic Specs

Dimension (Approx.)	W 123 x H 53 x D 135mm (4 7/8 x 2 1/8 x 5 3/8 inches)
Weight (Approx.)	400g (14.1oz)
Operating Temperature	+0 to +40°C (+32 to +104°F)
Storage Temperature	-20 to +60°C (-4 to +140°F)

AC Power Requirements

Voltage	100-240V
---------	----------

Frequency	50/60Hz
-----------	---------

DC Power Requirements

Voltage	12/24V
---------	--------

Power Consumption

Power Consumption	33-43VA (BATT), 40-53VA (VCR/CAMERA)
-------------------	--------------------------------------

Adapter

Output Voltage in Operating Mode	DC8.4V / 2.0A
----------------------------------	---------------

Charging Specs

Output Voltage in Charging Mode	DC8.4V / 1.6A
---------------------------------	---------------

Quick Charge	Quick Charge
--------------	--------------

Intelligent Display (LCD)	Y
---------------------------	---

DC Charge	Y
-----------	---

Charging Time

NP-F970 (Full Charge / Normal Charge)	345 min / 285 min
------------------------------------------	-------------------

NP-F960 (Full Charge / Normal Charge)	295 min / 235 min
------------------------------------------	-------------------

NP-F950 (Full Charge / Normal Charge)	260 min / 200 min
------------------------------------------	-------------------

NP-F930 (Full Charge / Normal Charge)	245 min / 185 min
------------------------------------------	-------------------

NP-F770 (Full Charge / Normal Charge)	245 min / 185 min
------------------------------------------	-------------------

NP-F750 (Full Charge / Normal Charge)	205 min / 145 min
------------------------------------------	-------------------

NP-F730 (Full Charge / Normal Charge)	195 min / 135 min
------------------------------------------	-------------------

NP-F730H (Full Charge / Normal Charge)	205 min / 145 min
-------------------------------------------	-------------------

NP-F570 (Full Charge / Normal Charge)	170 min / 110 min
------------------------------------------	-------------------

NP-F550 (Full Charge /	145 min / 85 min
------------------------	------------------

Normal Charge)

NP-F530 (Full Charge / Normal Charge)	140 min / 80 min
------------------------------------------	------------------

NP-F330 (Full Charge / Normal Charge)	115 min / 55 min
------------------------------------------	------------------

Eco-info (It is indicated from the high order of priority)

Use of lead-free solder (use 100% in weight)	Lead-free solder is used for soldering
-------------------------------------------------	-------------------------------------------

Reduction and phase- out of halogenated flame retardant (100%)	Halogenated flame retardants are not used in cabinets and in printed wiring boards
-------------------------------------------------------------------------	------------------------------------------------------------------------------------------

Gallery

