

LKRM-U331

6 x 330W 4K digital cinema projection lamp



Overview

6 x 330W High Pressure Mercury Lamp

The single replacement lamp for the LKRM-U331 is the LKRM-U331S

Specifications

General

| | |
|-------------------|--|
| Dimensions(W/H/L) | Approx. 89 x 122 x 148 mm (3.5 x 4.8 x 5.8 inches) |
| Mass. | Approx. 510 g (1.1 lb) |

Notes

Environmental notice for customers in the USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information.

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

Gallery



dimension are approximate. All trademarks are the property of their respective owners.