

ECM-322BMP

Ear-set Electret condenser microphone



Overview

The ECM-322BMP is an earset microphone, ideal for a variety of multimedia presentation applications ranging from seminars, conferences to lectures and workshops.

Features

Optimum Sound Pickup

Incorporating an omni-directional microphone capsule for reduced pop-and-wind noises, the ECM-322BMP earset microphone delivers a high sensitivity of -43 dB (7.1 mV) (*1) and allows clear voice pickup from any direction. (*1) 0 dB=1 V/Pa, at 1 kHz

Ear-Clip Style

Featuring an ear-clip style design, the ECM-322BMP earset microphone can be worn on either the left or right ear.

Adjustable Microphone Position

The slim and flexible microphone boom allows perfect positioning of the ECM-322BMP microphone.

Secure and Comfortable Fit

With its soft-texture ear hook, the ECM-322BMP earset microphone is comfortable to wear and fits stably on the ear, even during lengthy presentations.

Compact and Lightweight Design

The ECM-322BMP has been designed as a compact and ultra-lightweight earset microphone, weighing only 15 g (0.5 oz) (*2). (*2) Excluding the cable

Supplied with a 3-pole mini-jack with a stable lock mechanism

Supplied with 3-pole mini-jack with a stable lock mechanism for use with the UWP series bodypack transmitter.

Specifications

Audio Section

Capsule Type	Electret Condenser
Frequency Response	50 Hz to 18 kHz
Directivity	Omni-directional
Sensitivity *[1]	-42 dB (7.91 mV) \pm 3 dB
Output Impedance *[2]	1.4k Ω \pm 30%, Unbalanced
Dynamic Range	81 dB or more

Audio Section

Signal-to-Noise Ratio *[3]	60 dB or more
Inherent Noise *[4]	34 dB SPL or less
Wind Noise *[5]	55 dB SPL or less
Maximum Input Sound Pressure Level *[6]	115 dB SPL

General Section

Connector	BMP type. Supplied with ø3.5 mm, 3-pole mini plug.
Mic Cable	3.9 feet 1.2 m
Power Requirements	DC 2 V to 10 V
Power Consumption	1.3 mA or less
Dimensions *[7]	ø8.4 x 168 mm (Mic head) ø11/32 x 6 5/8 inches (Mic head)
Mass	Approx. 10 g without connectors Approx. 0.4 oz without connectors
Supplied Accessories	Operating instructions (1) Headband (1) Clip (1) Carrying case (1)

Notes

Note	*[1] 0 dB = 1 V/Pa, at 1 kHz *[2] Output impedance at 1 kHz *[3] A-weighted, 1 kHz, 1 Pa. *[4] 0dB SPL = 20? Pa. *[5] Wind noise at 2m/s (0 dB SPL = 20?Pa.) *[6] 0 dB SPL = 20? Pa. *[7] The values for dimensions are approximate.
------	--

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

Related products



UWP-D11

UWP-D bodypack wireless microphone package



UWP-D12


UWP-D handheld wireless microphone package



UWP-D16

UWP-D bodypack and XLR plug-on wireless microphone package

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.