

PSS-650P

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range

| | |
|------------------|------------------------------------------------------------------------------|
| | 1,000~1,675 mm / 39 3/8~65 15/16 inches |
| Up/down position | 650~975 mm / 25 19/32~38 3/8 inches (cut) |
| | 1,700~2,975 mm / 66 15/16~117 1/8 inches (x 2 units) (25mm pitch adjustment) |

Dimensions (W x H x D)

| | |
|------------------------|-------------------------------------------------|
| Dimensions (W x H x D) | 51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches |
|------------------------|-------------------------------------------------|

Dimensions (W x H x D) *without protrusions (Adjustment knob)

Dimensions (W x H x D)
*without protrusions
(Adjustment knob) 51 x 695 x 58.5 mm / 2 x 27 3/8 x 2
5/16 inches

Mass

Mass Approx. 2.2 kg / 4.8 lb

Maximum load

Maximum load 30 kg / 66 lb

Note

Note Max: up to 2 units connection

Color

Color Black

Gallery

