

## RCP-1500

Joystick type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



### Overview

The RCP-1500 remote control panel incorporates an LCD display with direct operation switches and a touch panel, which makes it a remote control panel that offers both ease of operation and multi-functionality that compares favorably with the MSU. The iris and master black adjustment block employs joystick type control. Up to four units can be mounted in a 19-inch EIA rack.

### Features

#### **Touch panel and many direct access switches suitable for various camera operations**

This remote control panel is equipped with the control functions required to perform various camera operations enabling the simple and accurate operation of various functions. The operation buttons, adjustment knobs, and other controls are arranged on the panel according to function and frequency of use. Guard frames are provided around buttons that are vital to the operation and setup of cameras to prevent the buttons from being unintentionally operated

#### **Ethernet connection capability**

It is possible to connect by LAN cable in addition to connecting using CCA-5 cable. Therefore, when setting up a multi-camera control system, not only can a system be built using the CNU-700 as previously, but a system can also be built using a LAN.

## Direct Scene file control

Easily access Scene file to support various scene setting.

## Customisable switch and menu.

User's can assign any function to a spare switch and also make their own favourite menu as well.

## Specifications

### General

Power consumption	4 W
-------------------	-----

Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
-----------------------	---------------------------------

Dimensions (W x H x D) (excluding protrusions)	102 × 310 × 125 mm (4 1/8 × 12 1/4 × 5 in)
---	--

Mass	1.8 kg (3 lb. 15 oz.)
------	-----------------------

Power supply	DC 10.5 V to 30 V
--------------	-------------------

### Input/output connectors

Ethernet	RJ-45 8-pin (X1)
----------	------------------

CCU/CNU	Multi-connector 8-pin, female (x1)
---------	------------------------------------

AUX	Multi-connector 8-pin, female (x1)
-----	------------------------------------

EXT I/O	D-sub 9-pin, female (x1)
---------	--------------------------

## Related products



### BRC-H900

Full HD robotic studio camera with 1/2-type Exmor 3CMOS sensor and 14x optical zoom



### CNA-1

Camera control network adaptor



### BRC-H800

Premium Full HD PTZ Camera with 12x optical zoom and uncompromising broadcast picture quality



### HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



NETWORKED **LIVE**

### HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



NETWORKED **LIVE**

### HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

### HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

### HDC-3170

Three 2/3-inch CMOS sensors portable system camera for triax operation



### BRC-X400

Premium 4K30P IP PTZ Camera with 30x (w/CIZ) zoom and NDI®|HX capability for use in a wide range of environments



### MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



### MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



NETWORKED **LIVE**

### UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)

## Gallery

