

VPL-CX236

4,100 lumens XGA installation projector



Overview

Bright, high resolution images, with simple set-up and low running costs for schools or meeting rooms

The VPL-CX236 offers installation flexibility, energy efficiency with a low total cost of ownership, and high image quality, while boasting a stylish design that blends into any decor.

Image correction features and a lens shift/zoom capability enable users to easily fit any image onto the screen, even from an offset projection angle.

In addition, these installation projectors are thoughtfully designed for optimum energy efficiency with a reduced total cost of ownership. They feature an auto power saving function, picture muting function with lamp control technology, long-lasting lamp, and low power consumption.

Every model delivers high image quality. The VPL-CX236 offers 4,100 lumens* brightness and provides high image quality with XGA resolution.

With all the features and functionality that you expect from Sony – particularly easy installation and usability, energy efficiency and low maintenance, and dependable image quality – the VPL-

CX236 is ideal for mid- to large-size classrooms, conference rooms, and many similar environments.

* ISO 21118

Features

Bright, clear images with maximum 4,100 lumens colour light output

The projector's high light output ensures that presentations are seen clearly in any classroom or meeting room. Choose from three brightness modes to suit any environment – High for naturally white presentations in bright rooms, Standard for everyday use, and Low for watching video in darkened rooms.

1.66:1 to 2.41:1 throw ratio

The VPL-CX236 offers a 1.66 - 1.66:1 to 2.41:1 throw ratio, allowing installation in most larger classrooms or meeting rooms.

High resolution lens

The high resolution Advanced Crisp Focus (ACF) lens offers a large diameter and fine pitch to ensure clear, sharp pictures.

Fine lens shift

The projector's wide lens shift range means that the projector can be positioned closer to the ceiling, or horizontally offset to avoid ceiling obstacles.

3LCD BrightEra™ Technology

The projector's efficient 3LCD panel system is enhanced by advanced BrightEra™ technology by Sony. You'll see the difference with impressively bright, consistent, high resolution images and increased panel reliability.

XGA resolution for crisp, clear presentations

XGA (1024 X 768) 4:3 resolution offers plenty of detail: ideal for making presentations direct from a laptop or PC.

Quieter operation

Acoustic fan noise is reduced compared with previous models for even quieter operation.

Save energy at the touch of a button

Just push the ECO MODE button on the projector or remote commander to instantly access a range of energy-saving settings.

Auto Dimming

Projector brightness is gradually reduced automatically if there's no input signal, or after a pre-set time – cutting power consumption and saving energy bills. Brightness instantly returns to maximum when an input signal is detected.

Power Saving Picture Mute

Touch a button on the projector remote and the picture's muted instantly. Another touch and the projector's instantly powered back up to resume your presentation.

Vertical and Horizontal Keystone Adjustment

Keystone distortion of vertically up to +/- 30 degrees and horizontally up to +/- 20 degrees can be digitally corrected via the on-screen menu and/or remote commander. This allows images to be projected with their correct geometry, even when installation space is limited.

Advanced Geometric Correction

Each image corner and side can be grabbed and adjusted for a true, square fit - invaluable when projecting from an offset position.

Smart APA (Auto Pixel Alignment)

Phase, Pitch and Shift values are automatically optimised when using the projector with a PC source. These values can also be adjusted manually.

Auto Input Search

The projector automatically switches to the correct input, simplifying set-up and saving time.

Audio switcher facility

The projector can select between two audio sources, routing them via a variable audio output to the room amplification system.

Picture Freeze Function

Picture Freeze is useful if you need to look at other material on your PC's screen during presentations without the audience seeing it. Freeze the current image that's being projected, and use your PC independently from the projector display.

Get closer with Digital Zoom

Instantly magnify a selected portion of the screen by up to 4x for a really close-up view of images from a connected PC.

Off and Go

Touch a button at the end of your presentation and projector is turned off immediately, without going through a lengthy power-down cycle.

Direct Power On/Off

There's no need to go through Standby mode when powering up the projector: the projector activates as soon as power is supplied.

Security that's built in

Your investment's protected with security measures including password protection and physical anti-theft anchor points.

Specifications

Display System

3 LCD system

Display System

Display device

Size of effective display area	0.63" (16 mm) x 3, BrightEra, Aspect ratio: 4:3
--------------------------------	---

Number of pixels	2,359,296 (1024 x 768 x 3) pixels
------------------	-----------------------------------

Projection lens

Focus	Manual
-------	--------

Zoom - Powered/Manual	Manual
-----------------------	--------

Zoom - Ratio	Approx. x1.45
--------------	---------------

Throw Ratio	1.66:1 to 2.41:1
-------------	------------------

Lens shift - Powered/Manual	Manual
-----------------------------	--------

Lens shift - Range	Vertical : +/- 5%
--------------------	-------------------

Lens shift - Range	Horizontal : +/- 4%
--------------------	---------------------

Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage 245 W type

Recommended lamp replacement time *1

Lamp mode: High 3000 H

Lamp mode: Standard 4000 H

Lamp mode: Low 5000 H

Filter cleaning / replacement cycle (Max.) *1

Filter cleaning / replacement cycle (Max.) Same time as the lamp replacement is recommended

Screen size

Screen size 40" to 300" (1.02 m to 7.62 m)
(measured diagonally)

Light output

Lamp mode: High 4100 lm

Lamp mode: Standard 3100 lm

Lamp mode: Low 2200 lm

Color light output

Lamp mode: High 4100 lm

Lamp mode: Standard 3100 lm

Lamp mode: Low 2200 lm

Contrast ratio (full white / full black) *2

Contrast ratio (full
white / full black) 3100:1

Speaker

Speaker 10 W x 1 (monaural)

Displayable scanning frequency

Horizontal 19 kHz to 92 kHz

Vertical 48 Hz to 92 Hz

Display resolution

Computer signal input Maximum display resolution: UXGA
1600 x 1200 dots*3

Video signal input NTSC, PAL, SECAM, 480/60i,
576/50i, 480/60p, 576/50p, 720/60p,

720/50p, 1080/60i, 1080/50i

Color system

Color system NTSC3.58, PAL, SECAM, NTSC4.43,
PAL-M, PAL-N, PAL60

Key stone correction (Max)

Vertical +/- 30°

Horizontal +/- 20°

OSD language

OSD language 24-language (English, French,
German, Italian, Spanish,
Portuguese, Japanese, Simplified
Chinese, Traditional Chinese,
Korean, Russian, Dutch,
Norwegian, Swedish, Thai, Arabic
,Turkish, Polish, Vietnamese, Farsi,
Indonesian, Finnish, Hungarian,
Greek)

INPUT OUTPUT (Computer/Video/Control)

RGB / Y PB PR input connector:

INPUT A	Mini D-sub 15-pin (female) Audio input connector: Stereo mini jack
INPUT B	RGB input connector: Mini D-sub 15-pin (female) Audio input connector: Stereo mini jack
INPUT C	HDMI input connector: HDMI 19-pin, HDCP support
INPUT D	HDMI input connector: HDMI 19-pin, HDCP support
VIDEO IN	Video input connector: Pin jack Audio input connector: Pin jack (x2)
OUTPUT	Monitor output connector*4: Mini D-sub 15-pin (female) Audio output connector*5: Stereo mini jack (variable out)
REMOTE	D-sub 9pin (male)/RS232C
LAN	RJ-45, 10BASE-T/100BASE-TX

Acoustic noise

Lamp mode: Low 29 dB

Operating temperature / Operating humidity

Operating temperature / Operating humidity	0°C to 40°C (32°F to 104°F) / 20% to 80% (no condensation)
---	--

Storage temperature / Storage humidity

Storage temperature / Storage humidity	-10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)
---	--

Power requirements

Power requirements	AC 100 V to 240 V 3.5 A to 1.5 A, 50/60 Hz
--------------------	--

Power consumption

AC 100 V to 120 V	Lamp mode: High : 350 W
-------------------	-------------------------

AC 220 V to 240 V	Lamp mode: High : 330 W
-------------------	-------------------------

Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5 W (when “Standby mode” is set to “Low”)
-------------------	---

AC 220 V to 240 V	0.5 W (when “Standby mode” is set to “Low”)
-------------------	---

Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	3.0 W (LAN) (when "Standby Mode" is set to "Standard")
AC 220 V to 240 V	3.0 W (LAN) (when "Standby Mode" is set to "Standard")

Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	After about 10 minutes
---	------------------------

Heat dissipation

AC 100 V to 120 V	1194 BTU/h
AC 220 V to 240 V	1126 BTU/h

Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Approx. 406 × 113 × 330.5 mm (15 31/32 × 4 7/16 × 13 inches)
--	--

Mass

Mass	Approx. 5.6 kg (12 lb)
------	------------------------

Supplied accessories

Remote commander	RM-PJ8
------------------	--------

Optional Accessories

Replacement lamp	LMP-C240
------------------	----------

Notes

*1	This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used.
----	---

*2	The value is average.
----	-----------------------

*3	Available for VESA Reduced Blanking signal.
----	---

*4	From INPUT A and INPUT B.
----	---------------------------

*5	Works as an audio switcher function. Output from a selected channel not available in
----	--

standby.

Environmental notice
for customers in the
USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information.

Gallery

