

MSU-1000

Master setup unit, multi camera remote control panel for HDC / HSC cameras (horizontal type)



Overview

The MSU-1000 master setup unit is a control panel for camera configuration and maintenance. It is a horizontally-oriented device (as opposed to the MSU-1500, which has a compact, vertically oriented panel) and can control multiple camera systems, using either the CNU-700 Camera Command Network Unit, or using a LAN, in which case up to 96 cameras can be controlled.

This product contains pre-installed software and requires the purchase of licence keys to activate some functions.

Features

Large and flexible system configuration

The MSU-1000 is part of a family of products that provides flexibility in the configuration of large and small camera control systems.

Ethernet LAN capability

The MSU-1000 supports inter-connectivity using an Ethernet LAN as well as a CNU-700

Customisable Switch and menu

MSU-1000 users can map any function to an assignable switch or menu item

Specifications

General

Power supply	AC 100 - 240 V. 50/60 Hz 0.35 A (Max.) DC 10.5 - 17 V 1.2 A (Max.)
--------------	---

Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
-----------------------	---------------------------------

Dimensions (W x H x D) (excluding protrusions)	482 × 222 × 67 mm (19 × 8 3/4 × 2 3/4 in.)
---	--

Mass	Approx. 4.6 kg (10 lb. 2 oz.)
------	-------------------------------

Input/output connectors

Ethernet	RJ-45 8-pin (X1)
----------	------------------

CCU/CNU	Multi-connector 8-pin, female (x1)
---------	------------------------------------

AUX	Multi-connector 8-pin, female (x1)
-----	------------------------------------

EXT I/O	D-sub 50-pin, female (x1)
---------	---------------------------

AC IN	3-pin (x1)
-------	------------

DC IN	4-pin (x1)
-------	------------

Related products



HDC-P43

4K/HD POV Camera



NETWORKED **LIVE**

HDCU-3100

IP enabled next generation Camera Control Unit



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



NETWORKED **LIVE**

HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



NETWORKED **LIVE**

HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

HDC-3170

Three 2/3-inch CMOS sensors portable system camera for triax operation



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



NETWORKED **LIVE**

HDC-P31

HD compact POV system camera with enhanced remote features and advanced HDR workflows



NETWORKED **LIVE**

RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



NETWORKED **LIVE**

RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



NETWORKED **LIVE**

UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-

SNMP80 (SNMP for 8K
ST 2110), UKCU-IP01F
(Networked Media
Interface)

Gallery

