

## Tablets for TEOS

High specification Android tablet\* optimised for corporate applications



### Overview

#### **Power at your fingertips**

Available in a choice of four screen sizes, these tablets are a stylish addition to boardrooms, huddle spaces, meeting rooms and reception areas and make it easy to control signage applications. The 7” and 10” make perfect partners for room booking and meeting room management, while the 15” and 22” are ideally matched for virtual reception applications.

Each durably styled tablet features a powerful processor and capacitive touchscreen to assure smooth, 24/7 responsive operation. There’s a wide range of networking options, and power over Ethernet (7”, 10” and 15” models) simplifies installation with no need for AC power outlets and additional cabling.

\* Tablets for TEOS are third-party products not manufactured by Sony.

### Features

#### **Simple installation**

No AC power outlets\* and standard VESA for wall-mounts.

#### **Clear, bright screen**

The tablet’s high-quality IPS panel offers a crisp, clear view of meeting information.

### **Reliable 24/7 operation**

This commercial-grade Android tablet is optimised for the rigours of corporate and B2B applications, allowing reliable 24/7 operation.

### **Speedy, responsive operation**

The tablet's powerful processor ensures smooth, responsive operation.

### **Multi-point capacitive touchscreen**

The high-quality touch enabled display supports multi-touch operation, allowing extra flexibility in gestural control.

### **Versatile connectivity options**

Connect to corporate networks via LAN or Wi-Fi. Use the USB port to install applications or perform system updates.

### **Power over Ethernet**

Support for PoE (Power over Ethernet) simplifies installation and reduces additional cabling requirements.

### **Flexible VESA mounting**

Integral VESA mounting hardware simplifies secure, permanent installation on a wall or desktop.

### **RFID identification**

Integrate the RFID reader accessory (TEB-RFID) for identification control. A swipe of an NFC tag or card is processed instantly.

## Specifications

### Panel

Size (diagonal)

TEB-7XPL: 7"

TEB-10XPL: 10.1"

TEB-10SLB: 10.1"

	TEB-15XP: 15.6" TEB-22XP: 21.5"
Resolution	TEB-7XPL: 1024 x 600 TEB-10XPL: 1280 x 800 TEB-10SLB: 1280 x 800 IPS TEB-15XP: 1920 x 1080 TEB-22XP: 1920 x 1080
Brightness	TEB-7XPL: 240 cd/m <sup>2</sup> TEB-10XPL: 500 cd/m <sup>2</sup> TEB-10SLB: 500 cd/m <sup>2</sup> TEB-15XP: 300 cd/m <sup>2</sup> TEB-22XP: 250 cd/m <sup>2</sup>
Use	24/7 Commercial use
Viewing Angle	TEB-7XPL: H 140° / V 130° TEB-10XPL: H 160° / V 160° TEB-10SLB: H 160° / V 160° TEB-15XP: H 170° / V 170° TEB-22XP: H 160° / V 160°
Touch Type	TEB-7XPL: Projected Capacitive (5 pts) TEB-10XPL: Projected Capacitive (5 pts) TEB-10SLB: Projected Capacitive (5 pts) TEB-15XP: Projected Capacitive (10 pts)

pts)  
TEB-22XP: Projected Capacitive (10 pts)

## System and Connectivity

CPU	<p>TEB-7XPL: Cortex A53, Octa Core, RK3368H</p> <p>TEB-10XPL: Cortex A17, Quad Core, RK3288</p> <p>TEB-10SLB: Cortex A17, Quad Core, RK3288</p> <p>TEB-15XP: Cortex A17, Quad Core, RK3288</p> <p>TEB-22XP: Cortex A17, Quad Core, RK3288</p>
-----	---

System Memory	2GB DDR3 SDRAM
---------------	----------------

Internal Storage	<p>TEB-7XPL: 16GB eMMC Flash</p> <p>TEB-10XPL: 16GB eMMC Flash</p> <p>TEB-10SLB: 8GB eMMC Flash</p> <p>TEB-15XP: 16GB eMMC Flash</p> <p>TEB-22XP: 16GB eMMC Flash</p>
------------------	---

External Storage	<p>TEB-7XPL: -</p> <p>TEB-10XPL: SD-Card Slot</p> <p>TEB-10SLB: SD-Card Slot</p> <p>TEB-15XP: SD-Card Slot</p>
------------------	--

	TEB-22XP: SD-Card Slot
OS	Android 6
I/O Ports	<p>TEB-7XPL: Micro-USB / USB / RJ45 / POGO-Connector (bottom) / 12V DC-IN</p> <p>TEB-10XPL: Micro-USB / USB / HDMI-out / GPIO Port / 3.5 mm audio-out / RJ45 / POGO-Connector (3 sides) / 12 V DC-IN</p> <p>TEB-10SLB: USB Express port, (Micro) USB, HDMI-out / POGO-Connector (3 sides)</p> <p>TEB-15XP: Micro-USB / USB / HDMI-out / SPDIF/ GPIO Port / 3.5 mm audio-out / RJ45 / POGO-Connector (3 sides) / 12V DC-IN</p> <p>TEB-22XP: Micro-USB / USB / HDMI-out / SPDIF/ 3.5 mm audio-out / RJ45 / POGO-Connector (3 sides) / 12V DC-IN</p>
Network	<p>TEB-7XPL: LAN RJ45 / WiFi / BT 4.2</p> <p>TEB-10XPL: LAN RJ45 / WiFi / BT version 4.2</p> <p>TEB-10SLB: LAN RJ45 / WiFi / BT version 4.2</p> <p>TEB-15XP: LAN RJ45 / WiFi / BT 4.2</p> <p>TEB-22XP: LAN RJ45 / WiFi / BT 4.2</p>

---

PoE Support	<p>TEB-7XPL: IEEE 802.3af and 802.3at (advised) PoE+ switch</p> <p>TEB-10XPL: IEEE 802.3af and 802.3at (advised) PoE+ switch</p> <p>TEB-10SLB: IEEE 802.3af and 802.3at (advised) PoE+ switch</p> <p>TEB-15XP: IEEE 802.3af and 802.3at (advised) PoE+ switch</p> <p>TEB-22XP: IEEE 802.3bt Type 3 for PoE++ switch</p>
-------------	---

---

## Video and Audio Specifications

Video Support	MKV, TS, FLV, AVI, VOB, MPG, DAT, ASF, RM, MOV, 3GP, MP4, WMV
Audio Support	MP2, MP3, WMA, WAV, AAC, OGG, ASF
Photo Support	JPG, BMP, GIF
Microphone	<p>TEB-7XPL: Optional</p> <p>TEB-10XPL: Yes</p> <p>TEB-10SLB: Yes</p> <p>TEB-15XP: Yes</p> <p>TEB-22XP: Yes</p>
Speaker	<p>TEB-7XPL: 2 x 2 W</p> <p>TEB-10XPL: 2 x 2 W</p>

---

Speaker	TEB-10SLB: 2 x 3 W TEB-15XP: 2 x 3 W TEB-22XP: 2 x 3 W
---------	--

## Physical

Housing	Plastic Housing
---------	-----------------

LED Bar	TEB-7XPL: Yes, but not used for TEOS TEB-10XPL: Side TEB-10SLB: Surround TEB-15XP: - TEB-22XP: -
---------	--

Colour	TEB-7XPL: Black TEB-10XPL: Black & White TEB-10SLB: Black & White TEB-15XP: Black TEB-22XP: Black
--------	---

Weight	TEB-7XPL: 500g TEB-10XPL: 650g TEB-10SLB: 610g TEB-15XP: 1300g TEB-22XP: 4200g
--------	--

Dimensions (W x H x D)	TEB-7XPL: 188 x 120 x 24 mm TEB-10XPL: 255 x 181 x 25 mm TEB-10SLB: 255 x 181 x 25 mm
------------------------	---

	TEB-15XP: 388 x 242 x 28 mm TEB-22XP: 531 x 322 x 35 mm
Mounting	TEB-7XPL: VESA unique pattern TEB-10XPL: VESA 75 TEB-10SLB: VESA 75 TEB-15XP: VESA 100 TEB-22XP: VESA 100
Power Supply	TEB-7XPL: 12V / 2A (EU, UK, US) TEB-10XPL: 12V / 2A (EU, UK, US) TEB-10SLB: 12V / 2A TEB-15XP: 12V / 2A (EU, UK, US) TEB-22XP: 12V / 5A
Power Usage	TEB-7XPL: 4 ~ 11 Watt TEB-10XPL: 10 ~ 20 Watt TEB-10SLB: 10 Watt ~ Max 19.5 Watt TEB-15XP: 10 ~ 20 Watt TEB-22XP: 30 ~ 45 Watt
Manage for TEOS Compatibility (Optional Licenses)	
Room Booking	TEM-TA10
Digital Signage	TEM-TA10
Visitor Sign In	TEM-TA10



Corporate TV	TEM-TA10
Wayfinding	TEM-TA10
Room Control	TEM-TA10
Survey	TEM-TA10

## Accessories

TEB-RFID	RFID/NFC 13.56MHz Reader accessory (compatible with Mifare and EU brands)
GM-75	Glass Mount Bracket for TEB-7XPL, TEB-10XPL and TEB-10SLB
WM-25	Wall Mount Bracket VESA 75/100, compatible with all tablets
WM-75	Deskstand for tablets VESA 75 for TEB-7XPL, TEB-10XPL and TEB-10SLB
WM-100	Deskstand for tablets VESA 100 for TEB-15XP, and TEB-22XP
TDS-100	Deskstand for tablets VESA 100 for TEB-15XP and TEB-22XP
CAB-RJ45-TAB	Hooked RJ45 Cable for mounted tablets

---

KIO-10DSQPL-NT	Kiosk for tablets for TEB-10XPL and TEB-10SLB
KIO-22DSK-NT	Kiosk for tablets for TEB-22XP

---

## Other

Standard Warranty	TEB-7XPL: 3 years with Advanced Exchange by a new model
	TEB-10XPL: 3 years with Advanced Exchange by a new model
	TEB-10SLB: 3 years with Advanced Exchange by a new model
	TEB-15XP: -
	TEB-22XP: -

---

## Gallery

