


## Content Manager

\*Please contact your local sales representative for details.



### Overview

#### **Taking care of your precious content**

This content management software application simplifies the storage, retrieval and management of audio-visual content with Sony's Optical Disc Archive (ODA) system.

#### **A world of solutions**

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy, reliable access to your precious data is crucial – along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

### Features

#### **Safeguard your precious content**

Archive all your audio-visual materials to shelf-managed Optical Disc Cartridges.

#### **Easy content management**

Perform quick, easy browsing, searching and retrieval of archived contents.

#### **Offline cartridge management**

Manage a range of offline features, including printing cartridge labels.

#### **Automatic proxy and thumbnail creation**

Generates proxy videos and thumbnails for browsing and searching of shelf-managed ODA cartridges.

#### **Advanced search**

Perform powerful searches using speech-to-text script and/or face-recognition data.

#### **Checksum Archive**

Supports Checksum Archive function.

#### **Direct viewing**

Allows direct viewing of audio-visual material on Optical Disc Cartridge (requires installation of Catalyst Browse \*1)

\*Please update Optical Disc Archive Software to V3.1 or later when using Content Manager V2.3 or later

\*1: Please download Catalyst Browse from [www.sonycreativesoftware.com/catalystbrowse](http://www.sonycreativesoftware.com/catalystbrowse)

## Specifications

|                        |  |
|------------------------|--|
| Processor              | Intel Core i5 3Ghz or higher   |
| Memory                 | 4 GB or more   |
| HDD available capacity | <p>500 MB or more HDD free space is required for installation.</p> <p>About 300GB of HDD free space is required to archive 1,000 hours of data (the required free space depends on the number and format of files to manage).</p> <p>When extracting metadata from files on a cartridge, a hard disk drive with free space greater than the total size of the files from which metadata is being extracted is required. Therefore, the maximum free space required is equivalent to the capacity of the cartridge.</p> |
| OS                     | <p>Windows</p> <p>Microsoft Windows 7 Professional or later, 64-bit version</p> <p>Microsoft Windows 8 Pro or later, 64-bit version</p> <p>Microsoft Windows 8.1 Pro or later, 64-bit version</p> <p>Mac OS</p> <p>OS X 10.8 Mountain Lion</p> <p>OS X 10.9 Mavericks</p> <p>OS X 10.10 Yosemite</p>   |
| Web browser            | <p>Windows</p> <p>Microsoft Internet Explorer or Google Chrome</p> <p>Mac OS</p> <p>Safari or Google Chrome</p>  |
| Display Resolution     | 1280 x 960 pixels or more  |
| Driver                 | <p>Optical Disc Archive Software</p> <p>Download and use the latest version of Optical Discs Archive Software. Also, update the drive firmware to the latest version.</p> <p>NOTE:</p> <p>Optical Disc Archive Filer cannot be started when using Content Manager. To use Optical Disc Archive Filer, first terminate the Content Manager service and then start Optical Disc Archive Filer, (Optical Disc Archive Filer is included with Optical Disc Archive Software).</p>  |
| Other                  | <p>Apache Tomcat 7.0</p> <p>Java 7</p> <p>MySQL 5.6</p> <p>WebM Media Foundation Components (for Microsoft Internet Explorer)</p>  |

## Related products



### ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)

### ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.


### Optical Disc Archive Software (Driver)

\*Please contact your local sales representative for details.

### ODS-D380U

\*Please contact your local sales representative for details.

## Gallery



---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.