

CNA-2

Camera Control Network Adapter



Specifications

General	
Power requirements	LAN1 PoE (IEEE802.3af Type1 Class0 compliant): DC 37 V – 57 V CCU power supply (CCA): DC 10.5 V – 30 V EXT I/O (D-SUB): DC 10.5 V – 17 V DC 12V IN: DC 11.4 V – 12.6 V 9 W (main unit only, DC 12V IN)
Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
Storage temperature	–20 °C to +60 °C (–4 °F to +140 °F)
Dimensions (W x H x D)	100 mm × 42 mm × 181 mm (4 inches × 1 11/16 inches × 7 1/4 inches)
Weight	660 g (1 lb 7.3 oz)
Input/output connectors	
CCU	8-pin multi-connector, jack (1)
LAN 1 to 2	RJ-45 (2) 1000BASE-T: IEEE 802.3ab
USB	High Speed USB (USB2.0) (1)
Supplied accessories	
Supplied accessories	Before Using This Unit (1)

Related products



NETWORKED **LIVE**

HDC-3500

2/3-type 4K 3-CMOS sensor portable system camera with HD 4x HFR capability



NETWORKED **LIVE**

HDC-5500

2/3-type 4K 3-CMOS sensor portable system camera with 4K 4x HFR capability



NETWORKED **LIVE**

HDC-P50

2/3-type 4K 3-CMOS sensor POV system camera with HD 6x HFR capability



NETWORKED **LIVE**

HDC-P31

2/3-type 3-CMOS sensor POV system camera



NETWORKED **LIVE**

HDCU-5500

IP-ready Camera Control Unit (CCU) for HDC-5500 and HDC-3500/3100 series system camera



NETWORKED **LIVE**

HDCU-5000

Camera Control Unit (CCU) for HDC-5500 and HDC-3500/3100 series system cameras



NETWORKED **LIVE**

HDCU-3500

IP-ready Camera Control Unit (CCU) for HDC-3500 4K/HD system camera



NETWORKED **LIVE**

RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



NETWORKED **LIVE**

RCP-3100

Joystick type of remote control panel for HDC/HSC/HXC series cameras.
5 units in 19-inch EIA rack.



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



HDC-3500RV

2/3-type 4K 3-CMOS sensor portable system camera with pre-installed variable ND filter and HD 4x HFR capability



HDC-3500R

2/3-type 4K 3-CMOS sensor portable system camera with HD 4x HFR capability



HDC-5500R

2/3-type 4K 3-CMOS sensor portable system camera with 4K 4x HFR capability

Gallery



specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 5 2026