

XDCA-FX9

Extension Unit for FX9 camera



Overview

Enhanced operability with advanced networking, wireless audio* and RAW output**

Connecting directly to the PXW-FX9 camera with no cables needed, the XDCA-FX9 extension unit provides convenient additional features to enhance shooting convenience and flexibility.

The XDCA-FX9 allows easy fitting of BP-GL and BP-FL series batteries, extending camera operating times during the most demanding shoots.

Attaching quickly and easily to the rear of the PXW-FX9 via a MultiPin connector, the XDCA-FX9 provides advanced networking capabilities for streaming or file transfer via Ethernet or dual link cellular connection. It also allows the easy addition of high quality wireless audio via a wireless receiver slot.* Additional output connectors including timecode and D-tap are also provided.

16-bit RAW signals can be output directly from the XDCA-FX9 using a third-party external recorder.**

The XDCA-FX9's RJ45 Ethernet support enables wired RCP control*** of Exposure, White Balance and more. XDCA-FX9 can power *** B4 lens when used with optional LA-EB1.

** Requires PXW-FX9 Ver.2.0 or higher firmware.*

*** Requires PXW-FX9 Ver 2.1 or higher. QFHD output within Super35 image circle and QFHD 100, 120fps high frame rate is limited to 10-bit.*

**** Requires PXW-FX9 Ver.3.0 or higher. To connect LA-EB1 and XDCA-FX9, use LA-EB1 supplied cable.*

Features

Seamless attachment, superb ergonomics

The XDCA-FX9 attaches directly to the PXW-FX9 via MultiPin connector, with no additional cabling required. Shooting time is extended by compatibility with Sony BP-GL and BP-FL series batteries. When using larger lenses, the extension unit balances any possible front heaviness while increasing stability when the camera is shoulder mounted.

Advanced network capabilities

The built-in networking capabilities of the PXW-FX9 enable streaming and file transfer via Wireless LAN. The XDCA-FX9 adds QoS Streaming with Dual Link connection via multiplexing of two cellular networks or Ethernet connection to improve image quality and stability.

Wireless audio support*

Ideal for field-based news production, the extension unit adds a wireless audio receiver slot for compatibility with receivers such as DWX series and URX series.

** Requires PXW-FX9 Ver.2.0 or higher firmware release.*

16-bit RAW recording with external recorder**

Adding the XDCA-FX9 extension unit to the PXW-FX9 allows recording of 16-bit RAW footage from the camera on a third-party RAW recorder (available separately). RAW data is output directly via the extension unit's RAW interface.

*** Requires PXW-FX9 Ver 2.1 or higher. QFHD output within Super35 image circle and QFHD 100, 120fps high frame rate is limited to 10-bit.*

RCP remote control with Ethernet

The XDCA-FX9's RJ45 Ethernet support enables wired RCP control of Exposure, White Balance and more.

*Requires FX9 Ver 3.0 or higher

Related products



BP-GL65A

Lithium-ion battery pack 66 Wh capacity



BP-GL95A

Lithium-ion battery pack 95 Wh capacity



BP-FL75

Olivine long-lasting battery for F-series cameras



BP-FLX75

Olivine long-lasting battery with 76 Wh capacity



LA-EB1

B4 lens mount adaptor for FX9, FS7 and FS7II



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 9 2026