

ODBK-201

*Please contact your local sales representative for details.



Overview

The ODBK-201 is a power supply for the ODS-L30M/L60.

The ODBK-20X series can drive the ODS-D280F and the ODS-D77F.

A world of solutions

Related products



ODS-L30M

*Please contact your local sales representative for details.



ODS-L60E

*Please contact your local sales representative for details.



ODS-L100E

*Please contact your local sales representative for details.



ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



ODS-D77F



ODS-

Optical Disc Archive
fibre channel drive
unit for ODS-L30M
PetaSite scalable
library with transfer
speeds up to 1,150
Mbps (read) and 780
Mbps (write-once
disc) or 310 Mbps
(rewritable disc)

D380F

*Please contact your
local sales
representative for
details.

Gallery

