

## VPL-VW320ES

4K SXRD Home Cinema Projector with 1500 lumens brightness, HDR compatibility and premium white finish (colour availability may vary by country)



### Overview

#### **Seeing is believing: spectacular 4K clarity that everyone can enjoy**

Bring the immersive excitement of true 4K cinematic images into every living space. Available also in a contemporary premium white finish, the VPL-VW320ES Home Cinema projector makes a stylish addition to any interior.

Advanced SXRD panel technology delivers incredible 4K images with four times the resolution of Full HD. You'll experience rich colours, 1500 lumens brightness and high contrast ratio - for vibrant, detail-packed pictures with native 4K resolution that always look clear and sharp, even in daylight living rooms.

You're future-proofed with compatibility for the latest 4K standards, as well as compatibility with HDR (High Dynamic Range) - so you'll get the very best out of today's content, and tomorrow's.

The compact VPL-VW320ES fits neatly into any home theatre or living room, with low fan noise that won't disturb the show, wide zoom/lens shift range and a front-facing exhaust port for extra installation flexibility. The projector's long-lasting lamp is rated for an extra-generous 6,000 hours operation (in Low Mode), for fewer interruptions and reduced maintenance costs.

## Features

### **Cinematic 4K clarity with four times the detail of Full HD**

SXRD panel technology featured in our professional cinema projectors delivers native 4K (4096 x 2160) resolution images, with no artificial pixel enhancement. Every detail is clear and natural, without jagged edges or visible pixels.

### **High brightness and contrast**

With an impressive 1,500 lumens brightness and spectacular dynamic contrast range, 4K images are clear with bright highlights and rich, deep blacks – even in well-lit rooms.

### **Premium white finish**

The projector is also available in a stunning premium white finish that looks beautiful in any contemporary or traditional décor.

### **Smooth, fluid on-screen action**

Coupled with the panel's super-fast response rate, Motionflow technology means you'll see every detail with minimal blur - no matter how fast the action.

### **TRILUMINOS™ Display for wider, more natural colours**

Sony's TRILUMINOS™ Display technology accurately reproduces a much broader range of colours than a standard projector system. You'll see the difference with finely-reproduced tones and textures plus greater colour purity, depth and realism.

### **HDR Compatible**

Take full advantage of the latest content produced with HDR (High Dynamic Range) for extremely wide contrast with an even higher range of brightness levels.

### **Future-proofed support for latest standards**

The VPL-VW320ES can project content at up to 60 frames per second (fps) in 4K (at colour signal YCbCr 4:2:0 / 8 bit) for even smoother images with superior colour and realism. Support for

HDCP 2.2 lets you enjoy the latest 4K content services.

### **Reality Creation upscales movies to 4K**

As well as projecting native 4K content, the VPL-VW320ES upscales your Full HD Blu-ray™ or DVD movie collection to 4K with Reality Creation - Sony's Super Resolution processing technology that enhances lower-resolution content, and even upscales 3D movies to 4K resolution.

### **Compatible with 'Mastered in 4K' Blu-ray™ Discs**

Enjoy a near-native 4K experience with discs 'Mastered in 4K'. It's as close as you can get to the 4K-pixel resolution and expanded colour range of the original.

### **Long-lasting lamp**

6000 hour rated lamp operating life (in Low mode) means simpler maintenance, with fewer lamp swaps and reduced running costs.

### **Flexible home installation with wide zoom and shift lens**

The powered zoom lens with a 2.06x zoom ratio and wide lens shift range gives greater installation flexibility in any room size, even with high ceilings.

### **Front-facing fan**

With the fan exhaust positioned at the front of the projector, you don't need to worry about wall clearance and room for air inhale/exhaust when installing. This helps maximise throw distance, for the biggest possible projected images.

### **Industry standard RF 3D compatible**

The projector's built-in RF transmitter synchronises with any RF 3D glasses for wider coverage and greater stability, so there's no need for an external transmitter.

## Specifications

### Display System

Display System	4K SXRD panel, projection system
----------------	----------------------------------

### Display device

Size of effective display area	0.74" x 3
--------------------------------	-----------

Number of pixels	26,542,080 (4096 x 2160 x 3) pixels
------------------	-------------------------------------

### Projection lens

Focus	Powered
-------	---------

Zoom	Powered (Approx. x2.06)
------	-------------------------

Lens shift	Powered Vertical: +85% -80% Horizontal: +/-31%
------------	--

### Light source

Light source	High-pressure mercury lamp, 225 W type
--------------	--

### Recommended lamp replacement time \*1

Recommended lamp	6000 H (Lamp mode: Low)
------------------	-------------------------

replacement time

---

## Screen size

Screen size 60" to 300" (1,524 mm to 7,620 mm)

---

## Light output

Light output 1500 lm (Lamp mode: High) \*2

---

## Colour light output

Colour light output 1500 lm (Lamp mode: High) \*2

---

## Displayable scanning frequency

Horizontal 19 kHz to 72 kHz

---

Vertical 48 Hz to 92 Hz

---

## Display resolution

Computer signal input Maximum display resolution: 1920 x 1080 dots (HDMI Input only)

---

480/60p, 576/50p, 720/60p,  
720/50p, 1080/60i, 1080/50i,  
1080/60p, 1080/50p, 1080/24p,  
3840 x 2160/24p, 3840 x 2160/25p,

---

Video signal input	3840 x 2160/30p, 3840 x 2160/50p*3, 3840 x 2160/60p*3, 4096 x 2160/24p, 4096 x 2160/25p, 4096 x 2160/30p, 4096 x 2160/50p*3, 4096 x 2160/60p*3
--------------------	--

## OSD language

OSD language	17-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Arabic, Polish)
--------------	---

## INPUT OUTPUT (Computer / Video / Control)

HDMI1 / HDMI2	Digital (RGB/Y Pb/Cb Pr/Cr)
Trigger	Minijack, DC 12 V Max. 100 mA
Remote	RS-232C, D-sub 9-pin (female)
LAN	RJ45, 10Base-T/100BASE-TX
IR IN	Mini Jack
USB	DC 5 V, Max. 500 mA

## Acoustic noise

Acoustic noise	26 dB
----------------	-------

---

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	5°C to 35°C (41°F to 95°F) / 35% to 85% (no condensation)
---	---

---

## Storage temperature / Storage humidity

Storage temperature / Storage humidity	-20°C to +60°C (-4°F to +140°F) / 10% to 90% (no condensation)
---	---

---

## Power requirements

Power requirements	AC 100 V to 240 V, 3.5 A to 1.5 A, 50/60Hz
--------------------	---

---

## Power consumption

Power consumption	350 W
-------------------	-------

---

Standby	0.3 W (when "Remote Start" is set to "Off")
---------	---

---

	1.0W (LAN) (when "Remote Start" is set to "On")
--	---

---

Networked Standby      When a LAN terminal is not connected, it becomes a low power consumption mode (0.5 W).

---

## Standby Mode / Networked Standby Mode Activated

Standby Mode /  
Networked Standby      After about 10 Minutes  
Mode Activated

---

## Dimensions (W x H x D) (without protrusions)

Dimensions (W x H x D)      495.6 x 195.3 x 463.6 mm  
(without protrusions)      19 1/2 x 7 11/16 x 18 1/4 inches

---

## Mass

Mass      Approx. 14 kg / 31 lb

---

## Supplied accessories

Supplied accessories      RM-PJ28 Remote Commander (1)  
Size AA (R6) Manganese Batteries  
(2)  
Lens Cap (1)  
AC Power Cord (1)  
Operating Instructions (CD-ROM)

---



(1)  
Quick Reference Manual (1)

---

## Optional Accessories

3D Glasses      Please contact your Sony representative for specific models available in your region.

---

## Replacement lamp

Replacement lamp      LMP-H220

---

## Notes

\*1      The figures are expected maintenance time and not guaranteed. They will depend on the environment or how the projector is used.

---

\*2      The values are estimate.

---

\*3      YCbCr 4:2:0 / 8 bit

---

\*4      HDMI Input2 is compatible with HDCP 2.2.

---

Lamp in this product contains mercury. Disposal of these

---

Environmental notice  
for customers in the  
USA

materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see [www.sony.com/mercury](http://www.sony.com/mercury) for additional information.

---

## Gallery

