

## Betacam SX

Betacam SX is an efficient and reliable digital format that combines excellent picture quality with cost effectiveness.



### Overview

- Strengthened base film for more robust tape.**
- Thinner tape allows increased recording time.**
- Refined high density particle packing and advanced calendering systems optimises tape surface.**
- Ultra fine magnetic particles for high output**
- High durability and long head life, even under punishing conditions**
- Cleaning Tape: BCT-5CLN**

### Specifications

#### General Characteristics

|                  |                 |
|------------------|-----------------|
|                  | BCT-194SXLA: 10 |
|                  | BCT-184SXLA: 10 |
|                  | BCT-124SXLA: 10 |
|                  | BCT-94SXLA: 10  |
| Master Carton    | BCT-64SXLA: 10  |
| Quantity (piece) | BCT-62SXA: 50   |
|                  | BCT-32SXA: 50   |
|                  | BCT-22SXA: 50   |

|                           |  |
|---------------------------|--|
|                           | BCT-12SXA: 50<br>BCT-6SXA: 50  |
| Master Carton Weight (kg) | BCT-194SXLA: 7.7<br>BCT-184SXLA: 7.6<br>BCT-124SXLA: 7<br>BCT-94SXLA: 6.8<br>BCT-64SXLA: 6.5<br>BCT-62SXA: 15.2<br>BCT-32SXA: 13.8<br>BCT-22SXA: 13.3<br>BCT-12SXA: 12.8<br>BCT-6SXA: 12.6 |
| Playing time (min)        | BCT-194SXLA: 194<br>BCT-184SXLA: 184<br>BCT-124SXLA: 124<br>BCT-94SXLA: 94<br>BCT-64SXLA: 64<br>BCT-62SXA: 62<br>BCT-32SXA: 32<br>BCT-22SXA: 22<br>BCT-12SXA: 12<br>BCT-6SXA: 6            |
|                           | BCT-194SXLA: 707<br>BCT-184SXLA: 671<br>BCT-124SXLA: 456<br>BCT-94SXLA: 349<br>BCT-64SXLA: 241   |

|                 |                |
|-----------------|----------------|
| Tape length (m) | BCT-62SXA: 231 |
|                 | BCT-32SXA: 124 |
|                 | BCT-22SXA: 88  |
|                 | BCT-12SXA: 52  |
|                 | BCT-6SXA: 31   |

---

|               |                  |
|---------------|------------------|
| Weight (g)    | BCT-194SXLA: 720 |
|               | BCT-184SXLA: 710 |
|               | BCT-124SXLA: 655 |
|               | BCT-94SXLA: 630  |
|               | BCT-64SXLA: 600  |
|               | BCT-62SXA: 270   |
|               | BCT-32SXA: 240   |
|               | BCT-22SXA: 230   |
|               | BCT-12SXA: 220   |
| BCT-6SXA: 215 |                  |

---

## Magnetic Properties

|                             |       |
|-----------------------------|-------|
| Intrinsic coercivity (kA/m) | 125.0 |
|-----------------------------|-------|

---

|                  |       |
|------------------|-------|
| Retentivity (mT) | 245.0 |
|------------------|-------|

---

|                    |      |
|--------------------|------|
| Squareness (Br/Bm) | 0.85 |
|--------------------|------|

---

## Physical Properties

Thickness:

---

|   |       |
|---|-------|
| backcoating ( $\mu\text{m}$ )               | 1.0   |
| Thickness: base ( $\mu\text{m}$ )           | 11.0  |
| Thickness: magnetic layer ( $\mu\text{m}$ ) | 2.0   |
| Thickness: total ( $\mu\text{m}$ )          | 14.0  |
| Width (mm)                                  | 12.65 |

## Gallery

