

## BTA-801

### Portable Tuner Mount Adaptor



### Overview

- Allows a WRR-855A/855B to be mounted on a Sony professional camcorder
- Supplies DC power from a camcorder to the WRR-855A/855B via an incorporated DC/DC converter

### Specifications

#### Audio Section

Analog Output	XLR-3-11C type (x1)
---------------	---------------------

#### General

Power Requirements	DC 10 to 17 V (12 V nominal)
--------------------	------------------------------

Power Consumption	200 mA DC or less (at DC 7 V)
-------------------	-------------------------------

Operating Temperature	32°F to 122°F 0°C to 50°C
-----------------------	------------------------------

Storage/Transport Temperature	-4°F to +140°F -20°C to +60°C
-------------------------------	----------------------------------

Dimensions <sup>*[1]</sup>	$\phi 88 \times 142.5 \times 31.5$ mm (W x H x D) (including projecting parts) $\phi 3 \frac{1}{2} \times 5 \frac{5}{8} \times 1 \frac{1}{4}$ inches (W x H x D) (including projecting parts)
Mass	Approx. 6.3 Approx. 180 g
Supplied Accessories	Operating Instructions (1) DC power cable (1) Betacam attachment kit (1 set) -Holder (1) Bracket (1) Binding head screws (M4 x 6) (2)

## Notes

Note	<sup>*[1]</sup> The values for dimensions are approximate.
------	--

## Gallery

