

## ODS-L100E

\*Please contact your local sales representative for details.



### Overview

#### **PetaSite Optical Disc Archive scalable library**

The ODS-L100E is an expansion unit for the ODS-L30M master library unit that extends the size of a PetaSite Optical Disc Archive scalable library for broadcast, post production, editing and desktop operations. The unit holds up to a maximum of 101 cartridges and a built-in robotic mechanism in a 7U, 19-inch rack-mountable chassis.

#### **Expand library with up to five extension units attached to ODS-L30M**

The ODS-L60E extends the PetaSite Optical Disc Archive, operating alongside the ODS-L30M and ODS-L100E (cartridge only) extension units. A total of five extension units maximum can attach to the ODS-L30M to make up a single 42U library offering a maximum 535 cartridges (Approx. 1.76PB), depending on the extension units used.

#### **Ideal for deep archive and near-online archive**

The Sony Optical Disc Archive system is ideal for deep archive for very long term archiving, such as broadcaster archives where data tape does not provide the assurance or meet the need for write-once, very long-term archive requirements. It provides second copy archive at a remote site and is ideal for business continuity/disaster recovery, post house and production back-up and for video, film and stock footage archives or national

archives. The system can also be used for news and sports clips that need to be near-online and as an on-line browse and proxy clip store.

## **A world of solutions**

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy, reliable access to your precious data is crucial – along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

## Features

### **PetaSite Optical Disc Archive scalable library**

The ODS-L100E holds up to a maximum of 101 cartridges, and a built-in robotic mechanism in a 7U, 19-inch rack-mountable chassis.

### **Categorisation by cartridge**

The ODS-L100E contains up to 101 cartridges, you can use different cartridges per category or user.

### **Expand library with up to five extension units attached to ODS-L30M**

The ODS-L60E extends the PetaSite Optical Disc Archive, operating alongside the ODS-L30M and ODS-L100E (cartridge only) extension units. A total of five extension units maximum can attach to the ODS-L30M to make up a single 42U library offering a maximum 535 cartridges (Approx. 1.76PB), depending on the extension units used.

### **File Manager**

The PetaSite Optical Disc Archive library is connected to a host

computer via Ethernet, and the drive units installed in this library is connected to the host computer via fibre channel. After File Manager software is installed on a host computer, all operations are controlled with a web-based GUI from each client computer. It uses a simple Drag & Drop operation to archive and retrieve files and provides the opportunity for the user to add simple text metadata when archiving files.

## Easily integrated in existing library SAN infrastructure

Operations can be managed by HSM application allowing auto-operation on all Optical Disc cartridges. The PetaSite Optical Disc Archive system is a complimentary archive technology that can co-exist with any LTO or data tape library in a standard SAN infrastructure. It provides a cost effective, long term archiving solution.

### Related products



#### File Manager2

\*Please contact your local sales representative for details.



#### Optical Disc Archive Software (Driver)

\*Please contact your local sales representative for details.



#### ODBK-103

\*Please contact your local sales representative for details.



#### ODBK-203

\*Please contact your local sales representative for details.



#### ODBK-202

\*Please contact your



#### ODBK-201

\*Please contact your



#### ODS-L30M

\*Please contact your



#### ODS-D280U

local sales representative for details.



## ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.

local sales representative for details.



## ODS-L100E

\*Please contact your local sales representative for details.

local sales representative for details.



## ODS-D77F

Optical Disc Archive fibre channel drive unit for ODS-L30M PetaSite scalable library with transfer speeds up to 1,150 Mbps (read) and 780 Mbps (write-once disc) or 310 Mbps (rewritable disc)

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



## Optical Disc Archive Cartridge Generation 1

300GB\*, 600GB, 1.2TB and 1.5TB disc (Rewritable or Write once)  
 ODC300R, ODC300RE, ODC600R, ODC600RE, ODC1200RE, ODC1500R



## Optical Disc Archive Cartridge Generation 2

ODC-3300R 3.3TB write-once cartridge



## ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



## ODS-L60E

\*Please contact your local sales representative for details.



## ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



**File Server  
mode  
License  
for FM2**

\*Please contact your  
local sales  
representative for  
details.

**ODS-  
D380U**

\*Please contact your  
local sales  
representative for  
details.

## Gallery

