

## Optical Disc Archive Software (Driver)

\*Please contact your local sales representative for details.



### Overview

This PC utility supports read/write of files from a host computer connected to an ODS-D77U/D77F or ODS-D55U Optical Disc Archive Drive Unit.

Includes Utility and Filer software.

### Features

#### **Simple file read/write**

This simple utility software supports transfer of files from a connected PC to a Sony ODS-D77U/D77F or ODS-D55U Optical Disc Archive (ODA) Drive Unit.

### Specifications

OS: ODS-D55U/ODS-D77U

Microsoft Windows XP Professional  
Service Pack 3 or later

Microsoft Windows 7 Professional  
32-bit/64-bit version, Service Pack  
1 or later

Microsoft Windows 7 Ultimate 32-  
bit/64-bit version, Service Pack 1 or

Windows

later  
Microsoft Windows 8 Pro 32-bit/64-bit version  
Microsoft Windows 8.1 32/64-bit version  
Microsoft Windows Server 2008 R2  
Microsoft Windows Server 2012  
Microsoft Windows Server 2012 R2

---

Mac

Mac OS X 10.6.8 or later 32-bit/64-bit  
Mac OS X 10.7.4 or later 64-bit  
Mac OS X 10.8.4 or later  
Mac OS X 10.9  
Mac OS X 10.10/10.10.1

---

Linux

Red Hat Enterprise Linux 6.2 64bit  
Red Hat Enterprise Linux 6.3 64bit  
Red Hat Enterprise Linux 6.4 64bit  
Red Hat Enterprise Linux 6.5 64bit  
Red Hat Enterprise Linux 6.6 64bit  
Red Hat Enterprise Linux 7.0 64bit

---

Note

When CentOS is used, please ask sales contact of Sony

---

OS: ODS-D77F

Microsoft Windows Server 2008 R2

---

Windows	Microsoft Windows Server 2012 Microsoft Windows Server 2012 R2
---------	---

Linux	Red Hat Enterprise Linux 6.2 64bit Red Hat Enterprise Linux 6.3 64bit Red Hat Enterprise Linux 6.4 64bit Red Hat Enterprise Linux 6.5 64bit Red Hat Enterprise Linux 6.6 64bit Red Hat Enterprise Linux 7.0 64bit
-------	--

Note	When CentOS is used, please ask sales contact of Sony.
------	--

## Memory

Windows	32bits OS : 4GB or more 64bits OS : 2GBx(number of the units + 1) or more
---------	--

Mac	32bits OS : 4GB or more 64bits OS : 2GBx(number of the units + 1) or more
-----	--

Linux	64bits OS : 2GBx(number of the units + 1) or more
-------	---

## Hard-disk space

Windows/Mac/Linux	32bits PC : 16GB or more 64bits PC : 8GB + 16GBx(number of
-------------------	---

the units + 1) or more

## Interface

	Hi-Speed USB (USB 2.0): Hi-Speed USB (USB 2.0) host controller required.
ODS-D55U/ODS-D77U (USB)	SuperSpeed USB (USB 3.0): SuperSpeed USB (USB 3.0) host controller required. In the case of Mac, only built-in USB ports on Mac are supported.
ODS-D77F (Fibre Channel)	Fibre Channel host controller is required. Recommended controller: QLE2560 / QLE2562 (QLogic(r) PCIe-to-8Gbps Fibre Channel Adapter)

## Notes

These system requirements may not apply to all computers.  
When you use your ODS-D77U with a PC running on Windows 7 or Windows Server 2008 R2, it is recommended to install the following update program released by Microsoft.

## Notes

<http://support.microsoft.com/kb/2581464>  
Utilizing the Windows 7 or Windows Server 2008 R2 update program and Optical Disc Archive Software in combination, data reading/writing speed from ODS-D77U is improved.

1. Register and download the update program at the Microsoft support site described above.
2. Unzip and install the update program.

---

## Notes

- Necessary settings associated with the update program are made when Optical Disc Archive Software is installed:  
Consequently, there is no need to perform registry settings specified at the bottom of the above mentioned support site page.
- The update program will not affect other USB devices.
- The update program is solely dedicated to Windows 7 or Windows Server 2008 R2 OS.

## Related products



**ODS-D55U**



**ODS-**



**ODS-L30M**



**ODS-L60E**

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)

## D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.

\*Please contact your local sales representative for details.

\*Please contact your local sales representative for details.



## ODS-L100E

\*Please contact your local sales representative for details.

## ODS-D280U

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge

## ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge

## ODS-D77F

Optical Disc Archive fibre channel drive unit for ODS-L30M PetaSite scalable library with transfer speeds up to 1,150 Mbps (read) and 780 Mbps (write-once disc) or 310 Mbps (rewritable disc)



## Content Manager

\*Please contact your local sales representative for details.

## File Manager2

\*Please contact your local sales representative for details.

## Gallery

