

## SNC-VB642D

Outdoor bullet-type Full HD IP Network Camera with IR (V-Series)



### Overview

**Weather-resistant ‘bullet type’ fixed camera offering excellent Full HD quality, high frame rate recording and high sensitivity, plus image stabilisation and Advanced IR technology**

The SNC-VB642D is a weather-resistant, easy to install ‘bullet-type’ fixed network camera. It’s ideal for a wide range of outdoor security and surveillance tasks, from city centres, transport systems and retail centres to schools and colleges.

The camera captures crisp, low-noise Full HD images, even in challenging low-light conditions. The sensitive 1/2.8” type Exmor R CMOS image sensor is teamed with XDNR processing, improving low-light performance and achieving the minimum illumination of 0.006 lux (30 IRE) in colour mode. Video can be captured at a high maximum frame rate of 60fps – allowing smoother, more accurate viewing of moving objects such as people or vehicles.

View-DR expands dynamic range for significantly improved imaging in high-contrast and strongly backlit scenes, like sun-drenched offices or car park entrances. Image stabilisation keeps video images crisp and clear, even when the camera is subject to vibration on a mounting pole or bracket.

The camera can see in conditions of complete darkness, with built-in IR (infrared) illumination that's coupled with Advanced IR technology to capture near and far-away objects without overexposure. The SNC-VB642D can clearly capture objects in total darkness at distances up to 100m (30 IRE) from the camera.

The addition of SD card edge storage allows video/audio data to be recorded directly by the camera when triggered by an alarm event. This provides valuable redundancy in the event of temporary network failure: recording to the network server resumes automatically when normal network connection is restored.

Installation of the SNC-VB642D is simplified by the same familiar user interface, usability and form factor as previous-generation Sony V Series cameras. Designed for round-the-clock outdoor use, the unitised camera can operate in extreme temperatures and is IP66 rated for resistance to water and dust. The unique mounting arm simplifies installation with flexible two-axis adjustment of viewing angle. For extra convenience, a built-in sunshade helps cut glare for improved picture quality and contrast on brightly-lit days.

## Features

### **Vandal resistant**

The camera's vandal-resistant design meets the IK08 standard (protection against mechanical impact), making the SNC-VB642D ideal for use in environments where there's a risk of physical tampering or damage.

### **See every scene clearly with Full HD image quality**

View fine detail in a wide range of everyday video security and surveillance environments, from retail spaces to banks and schools. The sensitive 1/2.8" type Exmor R CMOS image sensor is teamed with XDNR processing, improving low-light performance

and achieving the minimum illumination of 0.006 lux (30 IRE) in colour mode.

### **Capture smooth, fluid movement at 60fps**

Video images can be captured at a high frame rate of 60fps, allowing precise analysis when stepping through recorded footage frame by frame. It's ideal for applications like city surveillance where it's essential to see what's happening with split-second accuracy.

### **Steadier, more stable video footage**

The in-built image stabiliser minimises the effects of camera shake – for example when the camera's pole mounted or subject to mechanical vibration. With clearer, more stable video images it's easier to see what's happening in any scene.

### **Don't miss that crucial moment with Intelligent Motion Detection and Face Detection**

In-built motion detection can trigger a range of actions, from storage and transfer of images to sounding of external alarms. False alarms caused by noise, weather and environment noise are minimised by a smart processing algorithm. Human face detection is also supported, allowing rapid indexing of recordings to find events where a face is visible in the scene.

### **Clear pictures in total darkness with Advanced IR**

Built-in IR illuminators assist with clearly capturing objects in total darkness at distances up to 100m (30 IRE) from the camera. View-DR technology ensures that clear black-and-white images can be seen both near and far from the camera without overexposure.

### **Better pictures, day or night**

True D/N (Day/Night) function automatically switches the camera to Day or Night mode, depending on ambient light levels.

### **Optimum picture quality in any situation**

A choice of selectable picture modes optimises camera settings

for best picture quality in a wide range of applications and lighting environments.

### **Recording quality to suit your network**

Select CBR (constant bitrate), VBR (variable bitrate) or VBR-with-cap compression modes for optimised recording quality depending on IP network conditions.

### **Edge recording on SD card for reliable operation**

SD card edge storage allows video/audio data to be recorded directly by the camera when triggered by an alarm event. This provides valuable redundancy in the event of temporary network failure: recording to the network server resumes automatically when normal network connection is restored.

### **Detect in confidence with Edge-based Analytics**

Powerful DEPA Advanced video analytics enhances Intelligent Motion Detection with rule-based alarm triggers, providing alerts with object filters like 'passing' and 'intrusion' to further reduce false alarms.

### **Reduce cabling costs with Power Over Ethernet (PoE)**

Power over Ethernet (PoE) allows the camera be powered by the same Ethernet cable that's used for data transfer, reducing installation complexity and costs.

### **View and control with your smartphone**

Remotely view live camera images with your Android or iOS smartphone or tablet. You don't even need to download a special app.

### **ONVIF (Open Network Video Interface Forum) compliance**

Support for ONVIF simplifies interoperability with other network video devices. The ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information

between network video devices, including automatic device discovery and video streaming.

### **Adjustable sunshade**

The integrated sunshade protects the lens from direct sun glare, making the camera particularly suitable for outdoor use in direct sunlight.

### **Easy installation and set-up**

The unitised camera can be installed easily, with no need for an additional adaptor box. Setup is simplified with quick focus/zoom adjustment and flexible two-axis adjustment of the camera's field of view.

### **Dependable all-weather operation**

The camera can operate reliably over a wide temperature range. Ideal for outdoor use, it is IP66 rated, water-proof and dust-tight.

## Specifications

### Camera

Image Sensor	1/2.8-type progressive scan Exmor R CMOS sensor
Number of Effective Pixels	Approx. 2.13 Megapixels
Signal System	NTSC/PAL (switchable)
Sync System	Internal synchronization
Minimum Illumination (50 IRE)	Color: 0.01 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps)

	B/W: 0 lx (IR LED On)
Minimum Illumination (30 IRE)	Color: 0.006 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0 lx (IR LED On)
Dynamic Range	Equivalent to 90 dB with View-DR technology
S/N Ratio (Gain 0 dB)	More than 50 dB
Gain	Auto
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Exposure compensation, Shutter speed, Iris
White Balance	ATW, ATW-PRO, Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual, Indoor, Outdoor
Lens	CS-mount varifocal lens
Easy Zoom	Yes
Zoom Ratio	Optical zoom 3x Digital zoom 4x Total zoom 12x

Easy Focus for Setup	Yes
Horizontal Viewing Angle	105.3° to 35.6°
Vertical Viewing Angle	56.9° to 20.1°
Focal Length	f = 3.0 mm to 9.0 mm
F-Number	F1.2 (Wide) to F2.1 (Tele)
Minimum Object Distance	300 mm
IR Illuminator	Yes Wave length (typical): 850 nm , IR LED: 20 pieces)
IR Working Distance (50 IRE)	60 m 197 ft.
IR Working Distance (30 IRE)	100 m 328 ft.
White-light LED Illuminator	Yes
LED Working Distance (50IRE)	7 m 23 ft.
LED Working Distance (30IRE)	11 m 36 ft.

## Camera Features

Day/Night	True D/N
Day/Night linked with Easy Focus	Yes
Image Rotate	90°, 270°
Mirroring	Yes
Wide-D	View-DR
Tone Correction	Visibility Enhancer
Noise Reduction	XDNR
Image Stabilizer	Electronic
Picture Mode	Yes
Privacy Masking (number)	20
Privacy Masking (shape)	Quadrangle formed by any four corner points
Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
Edge Storage	Yes
Voice Alert	Yes



Vandal Resistant	IK08
Ingress Protection	IP66
Superimpose Number	3 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo mark
Superimpose Language	English
Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai, Turkish, Polish

## Video

Resolution	1920 x 1080, 1280 x 720, 1024 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 360, 352 x 288, 320 x 184 (H.264, JPEG)
Compression Format	H.264 (High/Main/Baseline Profile), JPEG

Maximum Frame Rate	H.264: 60 fps (1920 x 1080) JPEG: 60 fps (1280 x 720)
--------------------	--

Bitrate Control Mode	CBR/VBR (selectable)
----------------------	----------------------

Range of Bit Rate Setting	64 Kbps to 32 Mbps
---------------------------	--------------------

Solid PTZ	Yes
-----------	-----

e-Varifocal	Yes
-------------	-----

Adaptive Rate Control	H.264
-----------------------	-------

Bandwidth Control	JPEG
-------------------	------

Multi streaming Capability	Yes (3)
----------------------------	---------

Number of Clients	20
-------------------	----

## Intelligent Video/Audio Analytics

Analytics Architecture	DEPA Advanced
------------------------	---------------

Intelligent Motion Detection	Yes
------------------------------	-----

Face Detection	Yes
----------------	-----

Tamper Alarm	Yes
--------------	-----

Scene Analytics	Passing, Intrusion, Left Object
-----------------	---------------------------------

Detection, Removed Object  
Detection

---

## Audio

Compression Format    G.711/G.726/AAC (16 kHz, 48 kHz)

---

## System Requirements

Operating System        Windows 7 (32/64 bit) Ultimate,  
Professional Edition  
Windows 8.1 Pro (32/64 bit)  
Windows 10 Pro (32/64 bit)

---

Processor                Intel Core i7 2.8 GHz or higher

---

Memory                 2 GB or more

---

Web Browser            Microsoft Internet Explorer Ver.  
11.0  
Firefox Ver. 50.1 (plug-in free viewer  
only)  
Google Chrome Ver. 55.0 (plug-in  
free viewer only)

---

SNC toolbox            Yes

---

SNC toolbox mobile    Yes

---

## Network

---

Protocols	IPv4, TCP, UDP, ARP, ICMP, IGMP*, HTTP, DHCP, DNS, NTP, RTP/RTCP, RTSP over TCP, SMTP over HTTP, IPv6, HTTPS, FTP (client), SNMP (v1, v2c, v3), SSL
-----------	---

\*SSM (Source Specific Multicast) is supported.

QoS	DSCP
Multicast Streaming Support	Yes
ONVIF Conformance	Profile S, Profile T
Authentication	IEEE802.1X

## Interface

Analog Video Output	BNC x1, 1.0 Vp-p, 75 Ω, unbalance, sync negative 700 TV lines (analog video)*2
Analog Monitor Output for Setup	Phono jack x1
Microphone Input	Mini jack (monaural)
Line Input	Mini jack (monaural)

Line Output	Mini jack (monaural) Maximum output level: 1 Vrms
Network Port	10BASE-T/100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x2, make contact, break contact
Alarm Output	x2, AC 24V/DC 24 V, 1 A (mechanical relay outputs electrically isolated from the camera)
Card Slots	SD x 1
Confirmed SD Card Type	Max. 256GB *3

## General

Power Requirements	12 V DC $\pm$ 10% 24 V AC $\pm$ 20%, 50 Hz/60 Hz IEEE802.3at compliant (PoE/PoE+ system)
Power Consumption	Max. 21 W (AC 24 V/DC 12V) Max. 17 W (IEEE802.3at (PoE+)) Max. 12.5 W (IEEE802.3af (PoE))
	-40°C to +60°C (LED Off, PoE+, AC 24 V, DC 12 V) -40°C to +50°C (LED On, PoE+, AC

Operating Temperature	24 V, DC 12 V)
	-10°C to +60°C (LED Off, PoE)
	-10°C to +50°C (LED On, PoE)
	-40°F to +140°F (LED OFF, PoE+, AC 24 V, DC 12 V)
	-40°F to +122°F (LED ON, PoE+, AC 24 V, DC 12 V)
	14°F to +140°F (LED OFF, PoE)
	14°F to 122°F (LED ON, PoE)
	<hr/>
Cold Start Temperature	-30°C to +60°C (LED Off; PoE+, AC24V, DC 12 V)
	-30°C to +50°C (LED On; PoE+, AC24V, DC 12 V)
	0°C to +60°C (LED Off, PoE)
	0°C to +50°C (LED On, PoE)
	-22°F to +140°F (LED Off, PoE+, AC 24 V, DC12V)
	-22°F to +122°F (LED On, PoE+, AC 24 V, DC 12 V)
	32°F to +140°F (LED Off, PoE)
	32°F to 122°F (LED On, PoE)
<hr/>	
Storage Temperature	-20°C to + 60°C -4°F to + 140°F
<hr/>	
Operating Humidity	20 % to 90 % (no condensation)
<hr/>	

Storage Humidity	20 % to 80 % (no condensation)
Built-in Heater	Yes
Dimensions (W x H x D)*1	93 mm × 93 mm × 180.9 mm 3 3/4 inches x 3 3/4 inches x 7 1/8 inches  φ140 mm x 313.4 mm (including arm) φ5 5/8 inches x 12 3/8 inches (including arm)
Mass	Approx. 1620 g Approx. 3 lb 9.1 oz
External Material	Front Cover: PC Rear Case: ADC12 Arm/Stand: ADC12 Lens Cover: PC Sunshield: PC
External Color	White 4.4BG 8.4/0.2 Black 3.9PB 0.3/1.0
	JATE Technical Standard (LAN) UL2044, IEC60950-1 (CB) VCCI (Class A), FCC (Class A), IC (Class A) Emission: EN55032 (Class A)

Safety Regulations	Immunity: EN55024+ EN50130-4 Emission: AS/NZS CISPR32 (Class A) KC EMC-TR
--------------------	--

---

Supplied Accessories	Template (1) Wrench (1) Waterproof tape (1) Safety Regulations (1) Operating Instructions - Download site Information (1)
----------------------	---

---

## Notes

*1	The values for dimensions are approximate.
----	--

---

*2	Monitor display ratio 4:3
----	---------------------------

---

*3	The maximum number of event recording in the SD card is 4000. It may not use the full capacity of the SD card, depending on the limitation set for the event recording.
----	---

---



## Gallery

